



APPROVED: _____
DATE: _____ TITLE: _____




Rev	AWO #	Description	Date	Appr
-		RELEASED	11/15/18	




NUT



WASHER
.020 [0.50] Thickness



RECOMMENDED MOUNTING HOLES



RECOMMENDED PCB LAYOUT

NUT	BRASS	GOLD
LOCK WASHER	BRASS	GOLD
INSULATOR	TEFLON	
BODY	BRASS	GOLD
CENTER PIN	BRASS	GOLD
INSULATOR	TEFLON	
BODY	BRASS	GOLD
PART NAME	MATERIAL	FINISH

SPECIFICATIONS:
Temperature Rating: -40°C to +85°C
PTFE Temperature Rating: -190°C to +260°C
Environmental:
Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES .X ± .10 Ø.X ± .10 .XX ± .020 Ø.XX ± .015 .XXX ± .015 Ø.XXX ± .010		ADAM TECH INTERCONNECTS 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710	
APPROVALS		DATE	
DRAWN	AY	11/15/18	
CHECKED	AC	11/15/18	
APPROVED			
TITLE		SMA R/A PCB MOUNT JACK, MALE PIN GOLD PLATED	
SIZE	PART NO.	REV.	
X	RF2-100D-T-00-50-G-HDW-RP	-	
REF:	S00291T	SCALE:	NTS
SHEET 1 OF 1			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[RF2-100D-T-00-50-G-HDW-RP](#)