


| Rev | AWO # | Description | Date | Appr |
|-----|-------|-------------|--------|------|
| - | | RELEASED | 3/7/14 | |

APPROVED: _____

DATE: _____ TITLE: _____



| | | |
|--------------|----------|--------|
| COUPLING NUT | ZINC | NICKEL |
| BODY | BRASS | NICKEL |
| DESCRIPTION | MATERIAL | FINISH |

SPECIFICATIONS:

Electrical:

Impedance: 75 ohm

Frequency range: 0-2 GHz

Working Voltage: 250 VRMS max.

Dielectric Withstanding Voltage: 500 VRMS min.

Contact Resistance: 5 Milliohms max. (Center Contact)

2 Milliohms max. (Outer Contact)

Insulator Resistance: 1000 Megohms min.

Environmental:

Lead free, RoHS compliant.



ADAM TECH

909 Rahway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

F MALE TWIST ON

TITLE

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES Holes
.X ± .10 ØXX ± .10
.XX ± .020 ØXXX ± .015
.XXX ± .015 ØXXX ± .010

APPROVALS

DATE

DRAWN

HR

3/7/14

CHECKED

SY

3/7/14

APPROVED

SIZE

PART NO.

REF:

S00054T

SCALE: NTS

SHEET 1 OF 1

REV.

-

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[RF4-89-X-05-75](#)