






APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	6/6/18	



RECOMMENDED P.C.B LAYOUT



Port Type

RF55-32X-T-00-50-A-SH

RF55-32X-T-00-50-B-SH

Type	Color	Item No
A	BLACK	RF55-32A-T-00-50-X-SH
B	WHITE	RF55-32B-T-00-50-X-SH
C	BLUE	RF55-32C-T-00-50-X-SH
D	BORDEAUX VIOLET	RF55-32D-T-00-50-X-SH
E	GREEN	RF55-32E-T-00-50-X-SH
F	BROWN	RF55-32F-T-00-50-X-SH
G	GREY	RF55-32G-T-00-50-X-SH
H	VIOLET	RF55-32H-T-00-50-X-SH
I	BEIGE	RF55-32I-T-00-50-X-SH
K	CURRY	RF55-32K-T-00-50-X-SH
Z	WATER BLUE	RF55-32Z-T-00-50-X-SH
L	CARMINE RED	RF55-32L-T-00-50-X-SH
M	PASTEL ORANGE	RF55-32M-T-00-50-X-SH
N	PASTEL GREEN	RF55-32N-T-00-50-X-SH

PLASTIC SHELL	PA66+30%GF	
INSULATOR	LCP	
INSULATOR	PTFE	
PIN CONTACT	PHOSPHOR BRONZE	GOLD
COVER	BRASS	NICKEL
BODY (FRONT)	BRASS	NICKEL
BODY (BACK)	BRASS	FOG TIN
DESCRIPTION	MATERIAL	FINISH

SPECIFICATIONS:

Electrical:

Frequency range: DC~4 GHz
Nominal Impedance: 50 ohms
Withstanding voltage: 335 V
Insulator Resistance: 1000 MΩ
Contact Resistance: 6 Milliohms max. (Center Contact)
1 Milliohms max. (Outer Contact)

Temperature Rating:

Operating temperature: -40°C to +85°C

Environmental:

Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE MILLIMETERS
TOLERANCES: EXCEPT AS NOTED
INCHES HOLES
.X ± 0.25
.XX ± 0.15
.XXX ± 0.05

Ø.XX ± 0.13

APPROVALS		DATE
DRAWN	AY	6/6/18
CHECKED	MY	6/6/18
APPROVED		

ADAM
TECH
INTERCONNECTS

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE

FAKRA PLUG SMB TYPE RIGHT ANGLE, FOR SMT

SIZE

X

PART NO.

RF55-32X-T-00-50-X-SH

REV.

-

REF: S00134C

SCALE: NTS

SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[RF55-32H-T-00-50-G-SH](#) [RF55-32F-T-00-50-G-SH](#) [RF55-32Z-T-00-50-A-SH](#) [RF55-32A-T-00-50-A-SH](#) [RF55-32D-T-00-50-A-SH](#) [RF55-32B-T-00-50-A-SH](#) [RF55-32C-T-00-50-A-SH](#) [RF55-32E-T-00-50-A-SH](#) [RF55-32G-T-00-50-G-SH](#)
[RF55-32M-T-00-50-A-SH](#) [RF55-32K-T-00-50-A-SH](#) [RF55-32L-T-00-50-A-SH](#) [RF55-32I-T-00-50-G-SH](#)