



Rev	AWO #	Description	Date	Appr
-		RELEASED	10/5/06	

APPROVED: _____
DATE: _____ TITLE: _____



NO	Description	Qty	Material	Finish
5	SHELL	1	BRASS	NICKEL
4	FERRULE	1	BRASS	NICKEL
3	DIELECTRIC	1	DELTRIN	NONE
2	PIN	1	BRASS	GOLD
1	BODY	1	BRASS	NICKEL

SPECIFICATIONS

Electrical

Nominal Impedance: 50 Ohms
Frequency Range: 0 – 4 GHz
Maximum Peak Voltage: 500V
Insulation Resistance: 5000 Mohms min @ 500 VDC
Dielectric Withstanding Voltage: 1500 VAC rms.
Environmental:
Lead free, RoHS compliant.
Recommended soldering temp: 235 for 5 sec.



ADAM TECH

909 Railway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

MINIATURE UHF, MALE CRIMP,
50 OHM, FOR RG58

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE MM [INCHES] TOLERANCES: EXCEPT AS NOTED		Holes		DATE	
.X	± .10	Ø.X	± .10		
.XX	± .020	Ø.XX	± .015		
.XXX	± .015	Ø.XXX	± .010		
APPROVALS					
DRAWN	SS	10/5/06			
CHECKED					
APPROVED					
TITLE		SIZE		REV.	
PART NO.		X		-	
REF:		RF9-01-D-01-50		SHEET 1 OF 1	
SCALE:		NTS			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[RF9-01-D-01-50](#)