





APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-	7723	RELEASED	5/31/05	
A	7723	UPDATED DRAWING	3/8/16	HR



SPECIFICATIONS:

Material:
 Insulator: PBT, glass reinforced, rated UL 94V-0
 Insulator color: Black
 Contacts: Brass
 Plating:
 Gold flash over Nickel underplate overall
 Electrical:
 Current rating: 3 Amps max.
 Contact resistance: 20 mohms max. initial
 Insulation resistance: 5,000 Mohms min.
 Temperature Rating:
 Operating temperature: -40°C to +105°C
 Environmental:
 Lead free, RoHS compliant



Positions: 02 thru 40

A = .100 [2.54] x No. of Positions + .020 [0.50]

B = .100 [2.54] x No. of Spaces

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES		ADAM TECH 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710		
.X ± .10	Ø.X ± .10			
.XX ± .020	Ø.XX ± .015			
.XXX ± .015	Ø.XXX ± .010			
APPROVALS		DATE		
DRAWN	SS	5/31/05		
CHECKED				
APPROVED				
TITLE		.100 [2.54] SINGLE ROW RECEPTACLE STRIP .335 [8.50] HEIGHT		
SIZE	PART NO.	REV.		
X	RS1-XX-G	A		
REF:	S00059T	SCALE:	NTS	SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[RS1-03-G](#) [RS1-05-G](#) [RS1-08-G](#) [RS1-12-G](#) [RS1-02-G](#) [RS1-06-G](#) [RS1-40-G](#) [RS1-11-G](#) [RS1-04-G](#) [RS1-10-G](#)
[RS1-09-G](#) [RS1-07-G](#)