


APPROVED: \_\_\_\_\_  
 DATE: \_\_\_\_\_ TITLE: \_\_\_\_\_

Rev	AWO #	Description	Date	Appr
-		RELEASED	6/1/05	
A		UPDATE DRAWING	1/20/17	AY/CH



#### SPECIFICATIONS:

##### Material:

Insulator: PBT, glass reinforced, rated UL 94V-0

Insulator color: Black

Contacts: Phosphor Bronze

Plating:

Gold flash over Nickel underplate overall

Electrical:

Current rating: 3 Amp

Contact resistance: 20 mohms max

Insulation resistance: 5000 Mohms min

Dielectric withstanding voltage: 500 VAC for 1 minute

Environmental:

Lead free, RoHS compliant.



A = .100 [2.54] x No. of Positions per Row  
 B = .100 [2.54] x No. of Spaces

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES                      HOLES .X            ± .10            Ø.X            ± .10 .XX          ± .020          Ø.XX          ± .015 .XXX       ± .015          Ø.XXX       ± .010			<b>ADAM TECH</b> 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710		
APPROVALS			TITLE		
DATE			.100 x .100 DUAL ROW RECEPTACLE STRIP RIGHT ANGLE, 3-SIDED CONTACT		
DRAWN	SS	6/1/05	SIZE X	PART NO. RS2BR-XX-G	REV. A
CHECKED			REF: S00059T	SCALE: NTS	SHEET 1 OF 1
APPROVED					

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[RS2BR-16-G](#) [RS2BR-18-G](#) [RS2BR-12-G](#) [RS2BR-06-G](#) [RS2BR-04-G](#) [RS2BR-02-G](#) [RS2BR-08-G](#) [RS2BR-14-G](#)  
[RS2BR-10-G](#) [RS2BR-20-G](#)