




6		5		4		3		2		1	
APPROVED: _____						Rev	AWO #	Description		Date	Appr
						-		RELEASED		11/23/18	



SD-MMNXX-FFBBL-SX0-000
7=IP67



SPECIFICATIONS:
Material:
Housing: PPS, rated UL 94V-0, Color: Black
Contacts: Phosphor Bronze, Gold Flash plated
Plug Shell: Zinc Alloy, Nickel plated
Locking collar: Zinc Alloy, Nickel plated
Spring 1: Stainless Steel
Spring 2: Stainless Steel
O-ring 1: EDPM
Back shell: Zinc Alloy, Nickel plated
Shielding: Phosphor Bronze, Nickel plated
O-ring 2: EDPM
Clamp: Brass, Nickel plated
O-ring 3: NBR, Color: Black
Strain relief collar: Nylon 66, rated UL 94V-0, Color: White
Tightneing collar: PPS, Color: Brown
Environmental:
Lead free, RoHS compliant



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED			ADAM TECH INTERCONNECTS			909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710	
INCHES .X ± .10 .XX ± .020 .XXX ± .015			HOLES Ø.X ± .10 Ø.XX ± .015 Ø.XXX ± .010			TITLE WATERPROOF CONNECTOR, FEMALE DIN, ASSEMBLY, LOCK TYPE, SOLDER	
APPROVALS DRAWN CHECKED APPROVED			DATE HR AC 11/23/18			SIZE X	
						PART NO. SD-MMNXX-FFBBL-SX0-000	
						REV. -	
						REF: S00298T	
						SCALE: NTS	
						SHEET 1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[SD-MMN03-FFBBL-S70-000](#) [SD-MMN06-FFBBL-S70-000](#)