

6

5

4

3



2

1


APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	11/23/18	



SD-MMNXX-MMBBL-SX0-000
7=IP67



SPECIFICATIONS:

Material:

Housing: PPS, rated UL 94V-0, Color: Black

Contacts: Phosphor Bronze, Gold Flash plated

Jack Shell: Zinc Alloy, Nickel plated

Back shell: Zinc Alloy, Nickel plated

Shielding: Phosphor Bronze, Nickel plated

O-ring 2: EDPM

Clamp: Brass, Nickel plated

O-ring 3: NBR, Color: Black

Strain relief collar: Nylon 66, rated UL 94V-0, Color: White

Tightneing collar: PPS, Color: Brown

Environmental:

Lead free, RoHS compliant



UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES HOLES

.X	± .10	Ø.X	±.10
.XX	± .020	Ø.XX	±.015
.XXX	± .015	Ø.XXX	±.010

APPROVALS

DATE

DRAWN	HR	11/23/18
CHECKED	AC	11/23/18
APPROVED		

ADAM
TECH
INTERCONNECTS

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE
WATERPROOF CONNECTOR, MALE DIN,
ASSEMBLY, LOCK TYPE, SOLDER

SIZE X	PART NO. SD-MMNXX-MMBBL-SX0-000	REV. -
-----------	------------------------------------	-----------

REF: S00200T	SCALE: NTS	SHEET 1 OF 1
--------------	------------	--------------

6

5

4

3

2

1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[SD-MMN03-MMBBL-S70-000](#) [SD-MMN06-MMBBL-S70-000](#)