





APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	4/29/16	
A		UPDATE DIM.	7/17/18	AY/RT



RECOMMENDED PCB LAYOUT



SPECIFICATIONS:

Material:

Insulator: Hi-Temp Thermoplastic, rated UL 94V-0

Insulator color: Black

Contacts: Phosphor Bronze

Plating:

Gold flash over Nickel underplate overall

Electrical:

Current rating: 0.75 Amp

Contact resistance: 20 mohms max

Insulation resistance: 1,000 Mohms min.

Dielectric withstanding voltage: 500 VAC

Temperature Rating:

-40°C to +105°C

Environmental:

Lead free, RoHS compliant



Positions: 04 thru 100

A= .031 [0.80] x No. of Positions per row + .008 [0.20]

B= .031 [0.80] x No. of Spaces per row

C= .031 [0.80] x No. of Positions per row - .063 [1.60]

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES .X ± .10 Ø.X ±.10 .XX ± .020 Ø.XX ±.015 .XXX ± .015 Ø.XXX ±.010			<div>ADAM TECH INTERCONNECTS</div> 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710	
APPROVALS			TITLE	
DRAWN		HR	.031 [0.80] X .047 [1.20] FEMALE HEADER, SMT, DUAL ROW, GOLD PLATED, .122 [3.10] HEIGHT	
CHECKED		CH	SIZE X	
APPROVED			PART NO. SRS2Y-XX-U-SMT	
			REV. A	
			REF: S00111C	
			SCALE: NTS	
			SHEET 1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[SRS2Y-20-U-SMT](#) [SRS2Y-16-U-SMT](#) [SRS2Y-12-U-SMT](#) [SRS2Y-10-U-SMT](#)