






APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	1/26/21	



SPECIFICATIONS:

Material:

Case: DAP, Rated UL94V-0

Plunger: Brass, color Black w/ O-Ring

Bushing: Brass, color Black w/ O-Ring

Movable Contact: Copper Alloy, Silver Plated

Terminal: Copper Alloy, Silver Plated

Electrical:

Rating: 6A @ 125VAC or 28V DC

3A @ 250VAC

Contact resistance: 10 mΩ max

Insulation resistance: 1,000 Mohms min

Dielectric withstanding voltage: 1,500V RMS @Sea level

Life: 50,000 cycles at full load




Temperature Rating:

Operating temperature: -30°C to +85°C

Environmental:

Sealed IP68 Rated

Lead free, RoHS compliant



BUTTON POSITION		
FUNCTION	ON	ON
TERMINALS	2-3	2-1

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED

INCHES	HOLES
.X ± .10	Ø.X ± .10
.XX ± .020	Ø.XX ± .015
.XXX ± .015	Ø.XXX ± .010

APPROVALS		DATE
DRAWN	LH	1/26/21
CHECKED	AC	1/26/21
APPROVED		

ADAM
TECH

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE
HIGH PERFORMANCE PUSH BUTTON SWITCH,
SPDT, ON-ON, SILVER PLATED, SOLDER TYPE

SIZE	PART NO.	REV.
X	SW-PB10-AAA1QE-4	-
REF:	S00198T	SCALE: NTS
SHEET 1 OF 1		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[SW-PB10-AAA1QE-4](#)