







APPROVED: \_\_\_\_\_  
 DATE: \_\_\_\_\_ TITLE: \_\_\_\_\_

Rev	AWO #	Description	Date	Appr
-		RELEASED	11/2/21	



RECOMMENDED  
PANEL CUT-OUT



CIRCUIT DIAGRAM  
(SPST) OFF-MOM

#### SPECIFICATIONS:

##### Material:

Bushing&Button: Stainless steel, Varnish polished

Base: PA

Contact Material: Silver Alloy, (2.0x0.5mm)

##### Electrical:

Switch Rating: 0.5A @ 220V AC

Contact resistance: 50 mΩ max initial.

Insulation resistance: 1000M ohms min.

Dielectric withstanding voltage: 1,500V, RMS 50Hz, 1min

Electrical Life: 50,000 cycles min.

##### Mechanical:

Operating Force: 4N

Nut Torque: 0.6Nm max.

Temperature Rating:

Operating temperature: -25°C to +55°C

Environmental:

IP65 Front Panel Protection

Lead free, RoHS compliant



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS  
ARE INCHES [MM]. TOLERANCES: EXCEPT AS NOTED

INCHES	HOLES
.X ± .10	Ø.X ± .10
.XX ± .020	Ø.XX ± .015
.XXX ± .015	Ø.XXX ± .010

DRAWN	WX	11/2/21
CHECKED	RC	11/2/21
APPROVED		

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY  
AND SHOULD NOT BE USED WITHOUT PRIOR WRITTEN  
PERMISSION FROM ADAM TECH

**ADAM  
TECH**

909 Rahway Avenue,  
Union, NJ 07083  
Phone: 908-687-5000  
Fax: 908-687-5710

TITLE SWITCH, ANTI-VANDAL, PUSH BUTTON, SPST,  
OFF-MOM, 16mm, FLAT BUTTON, MOMENTARY

SIZE X	PART NO. SW-PB7-01B32BFM	REV. -
REF: S00198T	SCALE: NTS	SHEET 1 OF 1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[SW-PB7-01B32BFM](#)