






APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	11/2/21	



SPECIFICATIONS:

Material:

Body: PA66, Rated UL94V-0

Bushing: Stainless Steel, Varnish polished

Button: Stainless Steel, Varnish polished

O-Ring: Silicone

Contact Material: Silver Alloy (4.80mm)

Terminal: Brass, Silver plated

Electrical:

Switch Rating: 16A @ 125V/250V AC

Contact resistance: 300 mΩ max.

Insulation resistance: 100M ohms min @ 500V DC.

Dielectric withstanding voltage: 1500 VAC for 1 Min.

Electrical Life: 10,000 cycles min at full load.

Temperature Rating:

Operating temperature: -30°C to +85°C

Environmental:

IP65 Front Panel Protection

Lead free, RoHS compliant



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS
ARE INCHES [MM]. TOLERANCES: EXCEPT AS NOTED

INCHES	HOLES
.X ±.10	ØX ±.10
.XX ±.020	ØXX ±.015
.XXX ±.015	ØXXX ±.010

DRAWN	JJ	11/2/21
CHECKED	RC	11/2/21
APPROVED		

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY
AND SHOULD NOT BE USED WITHOUT PRIOR WRITTEN
PERMISSION FROM ADAM TECH

ADAM
TECH

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE SWITCH, ANTI-VANDAL SEALED, PUSH BUTTON,
SPST, 19mm, LATCHING, .187 QUICK TERMINAL

SIZE X	PART NO. SW-PB7-05B22FR	REV. -
REF: S00198T	SCALE: NTS	SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[SW-PB7-05B22FR](#)