






APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	11/2/21	
A		UPDATE SPEC.	11/12/21	WX/RC



SW-PB7-06LB22FFRXXXXX

LED Ring Color		LED Voltage	
R	Red	6V	6V AC/DC
G	Green	12V	12V AC/DC
Y	Yellow	24V	24V AC/DC
O	Orange	110V	110V AC/DC
B	Blue	220V	220V AC/DC
W	White		

Current Ith	Non electrical inductive load		Inductive load	
	Resistive load	LED load	Inductive load	Electromotor load
Voltage UI				
AC250	15	2	10	3
DC8	15	4	10	6
DC30	10	4	10	4
DC125	0.6	0.1	0.6	0.1
DC250	0.3	0.05	0.3	0.05

SPECIFICATIONS:

Material:

Body: POM, Rated UL94V-0

Bushing: Stainless Steel, Varnish polished

Button: Stainless Steel, Varnish polished

Contact Material: Silver Alloy (4.8mm)

Terminal: Brass, Silver plated

Electrical:

Voltage rating: 220V

Contact resistance: 50 mΩ max.

Insulation resistance: 1000M ohms min @ 500V DC.

Dielectric withstanding voltage: 1500V RMS, 50Hz.

Electrical Life: 50,000 cycles min at full load.

Temperature Rating:

Operating temperature: -25°C to +55°C

Environmental:

IP65 Front Panel Protection

Lead free, RoHS compliant



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS
ARE INCHES [MM]. TOLERANCES: EXCEPT AS NOTED

INCHES		HOLES	
.X	±.10	Ø.X	±.10
.XX	±.020	Ø.XX	±.015
.XXX	±.015	Ø.XXX	±.010

DRAWN	JJ	11/2/21
CHECKED	RC	11/2/21
APPROVED		

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY
AND SHOULD NOT BE USED WITHOUT PRIOR WRITTEN
PERMISSION FROM ADAM TECH

**ADAM
TECH**

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE
SWITCH, ANTI-VANDAL, PUSH BUTTON, HIGH
CURRENT, SPDT, 19mm, LATCHING, ON-ON

SIZE X	PART NO. SW-PB7-06LB22FFRXXXXX	REV. A
REF: S00198T	SCALE: NTS	SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[SW-PB7-06LB22FFRG12V](#) [SW-PB7-06LB22FFRR12V](#)