










DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	10/27/21	
A		UPDATE DRAWING	8/12/22	WX/ACT



CIRCUIT DIAGRAM
(DPST) ON-OFF

SW-R2-3A-F-X-4

	Actuator Marking
1	
2	
3	
4	
5	

Replace "x" in P/N with the corresponding switch color and marking

SPECIFICATIONS:

Material:

Body: Nylon 66, Color Black, Rated UL 94V-0

Terminal: Brass, Silver plated

Button: Nylon 66, Solid color Black, White color markings.

Electrical:

Rating: 10A @ 125V AC

6A @ 250V AC

Contact resistance: 50 mohms max

Insulation resistance: 100 mohms min

Dielectric withstanding voltage: 1500V AC

Electrical Life: 10,000 cycles min.

Temperature Rating:

Operating temperature: T85

Environmental:

Lead free, RoHS compliant



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS
ARE INCHES [MM]. TOLERANCES: EXCEPT AS NOTED

INCHES		HOLES	
.X	± .10	Ø.X	±.10
.XX	± .020	Ø.XX	±.015
.XXX	± .015	Ø.XXX	±.010

DRAWN	WX	10/27/21
CHECKED	RC	10/27/21
APPROVED		

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY
AND SHOULD NOT BE USED WITHOUT PRIOR WRITTEN
PERMISSION FROM ADAM TECH

ADAM TECH

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE	SWITCH, ROCKER, DPST, ON-OFF, COLOR BLACK, PANEL MOUNT, .187" [4.8] SOLDER
-------	---

SIZE X	PART NO. SW-R2-3A-F-X-4	REV A
-----------	----------------------------	----------

REF: S00206C	SCALE: NTS	SHEET 1 OF 1
--------------	------------	--------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[SW-R2-3A-F-1-4](#)