


Rev	AWO #	Description	Date	Appr
-		RELEASED	9/27/21	

APPROVED: _____

DATE: _____ TITLE: _____



SPECIFICATIONS:

Material:

Movable contact: Copper Alloy, Silver plated

Terminals: Silver plated with outer layer in Gold plating

Electrical:

Rating: 5 Amps with resistive load @ 125VAC or 28VDC

2 Amps with resistive load @ 250VAC

Contact resistance: 10 mohms max initial

Insulation resistance: 1000 Mohms min

Dielectric withstanding voltage: 1500V RMS @ sea level

Electrical life: 50,000 make and break cycles at full load

Temperature Rating:

Operating temperature: -30°C to +85°C

Environmental:

IP Class: IP67

Lead free, RoHS compliant



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM]. TOLERANCES: EXCEPT AS NOTED

INCHES	HOLES
.X ±.10	ØX ±.10
.XX ±.020	ØXX ±.015
.XXX ±.015	ØXXX ±.010

DRAWN	OW	9/27/21
CHECKED	AC	9/27/21
APPROVED		

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY AND SHOULD NOT BE USED WITHOUT PRIOR WRITTEN PERMISSION FROM ADAM TECH

ADAM TECH

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE
MINIATURE TOGGLE SWITCH,
SPDT, ON-ON, SOLDER TYPE

SIZE X	PART NO. SW-T2-2B-A-T2-X-03	REV. -
REF: S00198T	SCALE: NTS	SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[SW-T2-2B-A-T2-S-03](#)