







APPROVED: _____
DATE: _____ TITLE: _____

| Rev | AWO # | Description | Date | Appr |
|-----|-------|---------------|----------|--------|
| - | | RELEASED | 8/11/21 | |
| A | | UPDATED SPEC. | 5/27/22 | JJ/MC |
| B | | UPDATED SPEC. | 11/22/22 | WX/AC1 |



2 WAY



3 WAY

SW-T2-4X-B-A2-MA2

B=ON-ON (2 WAY)

D=ON-(ON) (2 WAY)

E=ON-OFF-ON (3 WAY)

F=ON-OFF-(ON) (3 WAY)

G=(ON)-OFF-(ON) (3 WAY)

H=ON-ON-ON (3 WAY)

SPECIFICATIONS:

Material:

Body: Bakelite, Color: Red

Lever: Brass, Nickel plated

Terminal: Brass, Silver plated

Electrical:

Rating: 3A @ 250V AC

6A @ 125V AC

Contact resistance: 20 mΩ max

Insulation resistance: 1000 MΩ min (500VDC)

Dielectric withstanding voltage: 1500V AC for 1 minute

Electrical Life: 10,000 cycles

Temperature Rating:

Operating temperature: -25°C to +85°C

Environmental:

Lead free, RoHS compliant



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS
ARE INCHES [MM]. TOLERANCES: EXCEPT AS NOTED

| INCHES | HOLES |
|-------------|-------------|
| .X ± .10 | ØX ± .10 |
| .XX ± .020 | ØXX ± .015 |
| .XXX ± .015 | ØXXX ± .010 |

| | | |
|----------|----|---------|
| DRAWN | JJ | 8/11/21 |
| CHECKED | RC | 8/11/21 |
| APPROVED | | |

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY
AND SHOULD NOT BE USED WITHOUT PRIOR WRITTEN
PERMISSION FROM ADAM TECH

ADAM
TECH

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE SWITCH, TOGGLE MINIATURE, DPDT,
PCB VERTICAL TYPE

| | | |
|-----------|-------------------------------|--------------|
| SIZE X | PART NO. SW-T2-4X-B-A2-MA2 | REV. B |
| REF: - | SCALE: NTS | SHEET 1 OF 1 |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[SW-T2-4B-B-A2-MA2](#) [SW-T2-4E-B-A2-MA2](#)