





APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	11/26/18	
A		UPDATE SPEC.	2/18/23	WX/LL1



RECOMMENDED PCB LAYOUT



Poles: 01 thru 15

SPECIFICATIONS:

Material:

Insulator: PBT, rated UL 94V-0

Insulator color: Black

Cover: PC, rated UL 94V-2

Contacts: Copper Alloy, Tin plated

Screw: M5 Steel, Zinc plated

Electrical:

Voltage rating: 600 V

Current rating: 65 A

Contact resistance: 20 mohms

Insulation resistance: 1000 Mohms / DC500V

Dielectric withstanding voltage: 2,200 VAC for 1 minute

Mechanical:

Wire Range: 14~6 AWG

Torque: 2.5Nm/25.0lb.in

Temperature Rating:

-40°C to +130°C

Environmental:

Lead free, RoHS compliant.



linear dimension (Tolerances Standard)								—	∕	⊥
variable	to	over	over	over	over	over	over	to	over	over
range	6	10	30	60	100	160	to	10	100	100
tolerance	±0.20	±0.30	±0.50	±0.70	±1.00	±1.30	±1.60	0.10	0.30	0.60

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS
ARE INCHES [MM]. TOLERANCES: EXCEPT AS NOTED

INCHES	HOLES
.X ±.10	Ø.X ±.10
.XX ±.020	Ø.XX ±.015
.XXX ±.015	Ø.XXX ±.010

DRAWN	AY	11/26/18
CHECKED	AC	11/26/18
APPROVED		

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY
AND SHOULD NOT BE USED WITHOUT PRIOR WRITTEN
PERMISSION FROM ADAM TECH

ADAM
TECH

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE		TERMINAL BLOCK, .630 [16.00] PITCH W/ SNAP ON CLEAR COVER		
SIZE	PART NO.	TBU-XX-W3-CC		REV. A
REF:	S00067C	SCALE:	NTS	SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[TBU-02-W3-CC](#) [TBU-05-W3-CC](#) [TBU-06-W3-CC](#) [TBU-04-W3-CC](#) [TBU-03-W3-CC](#)