

6

5

4

3




2

1

APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	2/05/09	
A		REDRAWN	11/30/12	



SPECIFICATIONS:

Material:

Insulator: PBT, glass reinforced, rated UL 94V-0

Insulator color: Black

Cover: PBT, glass reinforced, rated UL 94V-0, Color: Black

Contacts: Phosphor Bronze

Shell: Brass, Tin plated

Spring Chip: Brass, Tin plated

Rear Shell: SPCC, Nickel plated

Plating:

Gold flash over Nickel underplate on contact area.

Tin over copper underplate on solder tails.

Electrical:

Operating voltage: 250 VAC max.

Current rating: 1.5 Amp max.

Contact resistance: 30 mohms max.

Insulation resistance: 1000 Mohms min.

Dielectric withstanding voltage: 750 VAC for 1 minute

Environmental:

Lead free, RoHS compliant.



ADAM TECH

909 Railway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

UNIVERSAL SERIAL BUS, A TYPE
QUAD PORT, RIGHT ANGLE

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES				Holes			
.X	± .10	Ø.X	± .10	.X	± .10	Ø.X	± .10
.XX	± .020	Ø.XX	± .015	.XX	± .020	Ø.XX	± .015
.XXX	± .015	Ø.XXX	± .010	.XXX	± .015	Ø.XXX	± .010
APPROVALS				DATE			
DRAWN	DY	2/05/09		CHECKED	CH	2/05/09	
APPROVED							
TITLE				SIZE			
QUAD PORT, RIGHT ANGLE				PART NO.			
REF: S00095T				SCALE: NTS			
SHEET 1 OF 1				REV. A			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[USB-A-Q-RA-SB](#)