





APPROVED: \_\_\_\_\_  
DATE: \_\_\_\_\_ TITLE: \_\_\_\_\_

Rev	AWO #	Description	Date	Appr
-		RELEASED	12/3/04	
A		RE-DESIGNED SHELL AND INSULATOR	1/06/06	
B		ADDED DIM.	01/23/13	
C		UPDATE SHAPE	9/30/14	AY/YC
D		UPDATE CURRENT RATING	12/22/15	AY/SL
E		UPDATE CURRENT RATING	3/22/16	AY/YC



SPECIFICATIONS:  
Material:  
Insulator: PBT, rated UL 94V-0  
Insulator color: Black  
Contacts: Copper Alloy  
Shell: Copper Alloy, Nickel plated  
Plating:  
30u" Gold over Nickel underplate on contact area,  
Tin over Copper underplate on PCB tails  
Electrical:  
Voltage rating: 30 VAC  
Current rating: 1.5 Amp @ 250V AC  
Contact resistance: 30 mohms max.  
Insulation resistance: 1000 Mohms min. @ 500 VDC  
Dielectric withstanding voltage: 500 VAC  
Temperature Rating:  
Operating temperature: -20°C to +60°C  
Environmental:  
Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES .X ± .10 Ø.X ± .10 .XX ± .020 Ø.XX ± .015 .XXX ± .015 Ø.XXX ± .010			<b>ADAM TECH</b> 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710		
APPROVALS			TITLE UNIVERSAL SERIAL BUS SINGLE PORT, RIGHT ANGLE, PCB		
DRAWN	SS	10/4/04	SIZE X	PART NO. USB-A-S-RA-30	REV. E
CHECKED			REF: S00005C	SCALE: NTS	SHEET 1 OF 1
APPROVED					

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[USB-A-S-RA-30](#)