

6

5

4

3

2


1

| Rev | AWO # | Description | Date | Appr |
|-----|-------|-------------|---------|------|
| - | | RELEASED | 9/14/16 | |


APPROVED: _____

DATE: _____ TITLE: _____


D



C



B



B

SPECIFICATIONS:

Material:

Insulator: PBT, rated UL 94V-0

Insulator color: Black

Contacts: Copper Alloy

Shell: Steel, Nickel plated

Plating:

Gold flash over Nickel underplate on contact area

Tin over Copper underplate on PCB tails

Electrical:

Current rating: 1.5 Amp.

Voltage rating: 30 VAC.

Contact resistance: 30 mohms max.

Insulation resistance: 1000 Mohms min.

Dielectric withstanding voltage: 500 VAC.

Temperature Rating:

-35°C to +85°C

Environmental:

Lead free, RoHS compliant.

A

A

ADAM TECH

909 Rahway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

TITLE: UNIVERSAL SERIAL BUS, TYPE A, PCB

RIGHT ANGLE, BOARD LOCKS

| UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED | | | | INCHES | | | | Holes | | | |
|---|-------|----|-------|-------------------|--------|-----|--------|--------------|--------|------|--------|
| .X | ± .10 | ØX | ± .10 | .XX | ± .020 | ØXX | ± .015 | .XXX | ± .015 | ØXXX | ± .010 |
| APPROVALS | | | | DATE | | | | | | | |
| DRAWN | AY | | | 9/14/16 | | | | | | | |
| CHECKED | NC | | | 9/14/16 | | | | | | | |
| APPROVED | | | | | | | | | | | |
| SIZE | | | | PART NO. | | | | REV. | | | |
| X | | | | USB-A-S-RA-BL-CS8 | | | | - | | | |
| REF: S00126T | | | | SCALE: NTS | | | | SHEET 1 OF 1 | | | |

6

5

4

3

2

1



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[USB-A-S-RA-BL-CS8](#)