





Rev	AWO #	Description	Date	Appr
-		RELEASED	9/25/09	

APPROVED: \_\_\_\_\_

DATE: \_\_\_\_\_ TITLE: \_\_\_\_\_



RECOMMENDED PCB LAYOUT  
(BOTTOM VIEW)



SPECIFICATIONS:

Material:

Insulator: PBT, Glass filled, rated UL 94V-0

Insulator color: Black

Contacts: Phosphor Bronze

Shell: Brass, nickel plated

Plating:

Gold over Nickel underplate on contact area,  
Tin over Copper underplate on PCB tails.

Electrical:

Operating voltage: 30 VAC max.

Current rating: 1 Amp max.

Contact resistance: 30 mohms max.

Insulation resistance: 1000 Mohms min.

Dielectric withstanding voltage: 500 VAC for 1 minute

Temperature Rating:

Operating temperature: -20°C to +60°C

Environmental:

Lead free, RoHS compliant.



**ADAM TECH**

909 Rahway Avenue, Union, NJ 07083  
Phone: 908-687-5000 Fax: 908-687-5710

TITLE: UNIVERSAL SERIAL BUS, TYPE A  
FLAT, RIGHT ANGLE, DIP TYPE

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES				HOLES			
.X	± .10	Ø.X	± .10	.XX	± .020	Ø.XX	± .015
.XXX	± .015	Ø.XXX	± .010				
APPROVALS				DATE			
DRAWN	DY		9/25/09				
CHECKED							
APPROVED							
SIZE	PART NO.	REV.					
X		-					
REF:	S00095T	SCALE:	NTS	SHEET	1 OF 1		

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[USB-A-S-RA-FS](#)