





APPROVED: \_\_\_\_\_  
DATE: \_\_\_\_\_ TITLE: \_\_\_\_\_

Rev	AWO #	Description	Date	Appr
-		RELEASED	1/23/14	
A		REDRAWN	4/9/14	AV/LW



**SPECIFICATIONS:**  
Material: PBT, rated UL 94V-0  
Insulator color: White  
Contacts: Copper Alloy  
Shell: Copper Alloy, Nickel plated  
Back Shell: SPCC, Nickel plated  
Plating: Tin over Copper underplate on tails.  
Gold flash over Nickel underplate on contact area.  
Electrical:  
Current rating: 1.5A max  
Contact resistance: 30 mohms max  
Insulation resistance: 1,000 Mohms min  
Dielectric withstanding voltage: 500 VAC Max.  
Environmental:  
Lead free, RoHS compliant



**ADAM TECH**

909 Railway Avenue, Union, NJ 07083  
Phone: 908-687-5000 Fax: 908-687-5710

TITLE: USB, TYPE A, RIGHT ANGLE UPRIGHT  
THRU-HOLE, SELECTIVE GOLD

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES							
.X	± .10	Ø.X	± .10	HOLES	± .10		
.XX	± .020	Ø.XX	± .015				
.XXX	± .015	Ø.XXX	± .010				
APPROVALS				DATE			
DRAWN	AY		1/23/14				
CHECKED	EH		1/23/14				
APPROVED							
SIZE				PART NO.			
X				USB-A-S-RU-S4			
REF: S00097C				SCALE: NTS			
				SHEET 1 OF 1			
				REV. A			

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[USB-A-S-RU-S4](#)