





APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	12/3/04	
A		ADDED ROHS MARK	8/25/08	BAS
B		REDRAWN	12/08/09	
C		REVISED DIM.	5/30/11	
D		REVISED SPEC.	12/22/11	



SPECIFICATIONS:
Material:
Insulator: PBT, Glass filled, rated UL 94V-0
Insulator color: White
Contacts: Brass
Shell: Brass, nickel plated
Plating:
Gold over Nickel underplate on contact area,
Tin over Copper underplate on PCB tails
Electrical:
Operating voltage: 30 VAC max.
Current rating: 1.5 Amp max @ 250V AC.
Contact resistance: 30 mohms max.
Insulation resistance: 1000 Mohms max.
Dielectric withstanding voltage: 500 VAC for 1 minute
Temperature Rating:
Operating temperature: -20°C to +60°C
Environmental:
Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED				INCHES				Holes			
.X	± .10	ØX	± .10	.X	± .10	ØX	± .10	.X	± .10	ØX	± .10
.XX	± .020	ØXX	± .015	.XX	± .020	ØXX	± .015	.XX	± .015	ØXX	± .010
.XXX	± .015	ØXXX	± .010	.XXX	± .015	ØXXX	± .010	.XXX	± .015	ØXXX	± .010
APPROVALS				DATE				TITLE			
DRAWN				SS				10/4/04			
CHECKED											
APPROVED											
SIZE				PART NO.				REV.			
X				USB-A-S-VT-WT				D			
REF: S0005C				SCALE: NTS				SHEET 1 OF 1			

ADAM TECH
909 Railway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

UNIVERSAL SERIAL BUS
SINGLE PORT, VERTICAL, PCB

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[USB-A-S-VT-WT](#)