





APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED FOR NEW TOOLING	4/11/06	
A		REDRAWN	12/13/12	



SPECIFICATIONS:
Material:
Insulator: PBT, Glass filled, rated UL 94V-0
Insulator color: Black
Contacts: Brass
Shell: Brass, nickel plated
Plating:
Gold over Nickel underplate on contact area,
Tin over Copper underplate on PCB tails
Electrical:
Operating voltage: 30 VAC max.
Current rating: 1.5 Amp max @250V AC.
Contact resistance: 30 mohms max.
Insulation resistance: 1000 Mohms min.
Dielectric withstanding voltage: 500 VAC for 1 minute
Temperature Rating:
Operating temperature: -20°C to +60°C
Environmental:
Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED				ADAM TECH			
INCHES				909 Railway Avenue, Union, NJ 07083			
Holes				Phone: 908-687-5000 Fax: 908-687-5710			
X .10 ± .10 ØXX ± .10				UNIVERSAL SERIAL BUS, SINGLE PORT,			
XX .020 ± .015 ØXX ± .015				VERTICAL, PCB			
XXX .015 ± .010 ØXXX ± .010							
APPROVALS				TITLE			
DATE							
DRAWN				SIZE			
SS				PART NO.			
CHECKED				X			
APPROVED				USB-A-S-VTA			
REF:				SCALE: NTS			
S00005C				SHEET 1 OF 1			
				REV. A			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[USB-A-S-VTA](#)