






APPROVED: \_\_\_\_\_  
 DATE: \_\_\_\_\_ TITLE: \_\_\_\_\_

Rev	AWO #	Description	Date	Appr
-		RELEASED	5/10/13	
A		UPDATE SPEC.	2/26/21	LH/RT



RECOMMENDED PCB LAYOUT



**SPECIFICATIONS:**  
 Material:  
 Insulator: Hi-temp thermoplastic, rated UL 94V-0  
 Insulator color: Black  
 Contacts: Brass  
 Shell: Brass, Nickel plated  
 Plating:  
 Gold Flash over Nickel underplate on contact area,  
 Tin over Copper underplate on PCB tails  
 Electrical:  
 Operating voltage: 30 VAC max.  
 Current rating: 1.5 Amp max @250V AC.  
 Contact resistance: 30 mohms max.  
 Insulation resistance: 1000 Mohms min.  
 Dielectric withstanding voltage: 500 VAC for 1 minute  
 Temperature Rating:  
 -40°C to +85°C  
 Environmental:  
 Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES                      HOLES .X       ± .10                Ø.X       ± .10 .XX      ± .020              Ø.XX      ± .015 .XXX   ± .015              Ø.XXX   ± .010			<div>ADAM TECH</div>		909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710	
APPROVALS			DATE		TITLE UNIVERSAL SERIAL BUS, SINGLE PORT, VERTICAL, PCB	
DRAWN		AY	5/10/13			
CHECKED		YC	5/10/13			
APPROVED						
			SIZE X		PART NO. USB-A-S-VTA-HT	
			REF: S00005C		SCALE: NTS	
					SHEET 1 OF 1	

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[USB-A-S-VTA-HT](#)