





APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	3/19/15	
A		ADDED SPEC.	12/18/18	AY/IW



SPECIFICATIONS:

Material:

Insulator: Hi-temp thermoplastic, rated UL 94V-0

Insulator color: Black

Contacts: Phosphor Bronze

Shield: Brass, Nickel plated

Contact Plating:

Gold Flash over Nickel underplate on contact area,

Tin over Nickel underplate on SMT tails

Electrical:

Rated Voltage And Current: 1.5 A @ 250 VAC min

Contact resistance: 30 mohms max

Insulation resistance: 1,000 Mohms min @ 500 VDC

Dielectric withstanding voltage: 750 VAC for 1 minute

Temperature Rating:

Operating temperature: -55°C to +85°C

Environmental:

Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES .X ± .10 Ø.X ± .10 .XX ± .020 Ø.XX ± .015 .XXX ± .015 Ø.XXX ± .010			ADAM TECH INTERCONNECTS		909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710
APPROVALS DRAWN HR CHECKED NP APPROVED			DATE 3/19/15 3/19/15		
TITLE UNIVERSAL SERIAL BUS SINGLE PORT, RIGHT ANGLE, SMT			SIZE X	PART NO. USB-B-S-RA-TSMT-CS1	REV. A
REF: S00095T			SCALE: NTS	SHEET 1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[USB-B-S-RA-TSMT-CS1](#)