






Rev	AWO #	Description	Date	Appr
-		RELEASED	5/12/10	

APPROVED: \_\_\_\_\_

DATE: \_\_\_\_\_ TITLE: \_\_\_\_\_



RECOMMENDED PCB LAYOUT  
(TOP VIEW)

SPECIFICATIONS:

Material:

Insulator: PBT, glass filled, rated UL 94V-0

Insulator color: White

Contacts: Phosphor Bronze

Shell: SPCC, Nickel plated

Plating:

Gold flash over Nickel underplate on contact area,  
Tin over Copper underplate on PCB tails

Electrical:

Operating voltage: 30 VAC

Current rating: 1.5 Amp @ 250V AC

Contact resistance: 30 mohms max

Insulation resistance: 1000 Mohms min

Dielectric withstanding voltage: 500 VAC for 1 minute

Temperature Rating:

Operating temperature: -20°C to +60°C

Environmental:

Lead free, RoHS compliant.



**ADAM TECH**

909 Rahway Avenue, Union, NJ 07083  
Phone: 908-687-5000 Fax: 908-687-5710

TITLE

USB, TYPE B, SINGLE PORT, RIGHT ANGLE,  
THRU-HOLE, COLOR WHITE, SPCC SHELL

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE MM [INCHES] TOLERANCES: EXCEPT AS NOTED INCHES HOLES				<b>ADAM TECH</b>			
.X	± .10	ØX	± .10	909 Rahway Avenue, Union, NJ 07083			
.XX	± .020	ØXX	± .015	Phone: 908-687-5000 Fax: 908-687-5710			
.XXX	± .015	ØXXX	± .010	TITLE			
APPROVALS				USB, TYPE B, SINGLE PORT, RIGHT ANGLE, THRU-HOLE, COLOR WHITE, SPPC SHELL			
DRAWN		DY	5/12/10	SIZE			
CHECKED				PART NO.		REV.	
APPROVED				X		-	
REF: S00015C				SCALE: NTS		SHEET 1 OF 1	

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[USB-B-S-RA-WT-SPCC](#)