


APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	8/18/11	
A		UPDATED DIM.	9/14/17	HR/TY



SPECIFICATIONS:

Material:

Insulator: PBT, Glass filled, rated UL 94V-0

Insulator color: Black

Contacts: Phosphor Bronze

Shell: Copper Alloy, nickel plated

Plating:

30u" Gold flash over Nickel underplate on contact area,

Tin over Copper underplate on PCB tails

Electrical:

Voltage rating: 30 VAC

Current rating: 1.5 Amp

Contact resistance: 30 mohms max.

Insulation resistance: 1000 Mohms min.

Dielectric withstanding voltage: 500 VAC

Temperature Rating:

Operating temperature: -20°C to +60°C

Environmental:

Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED			ADAM TECH 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710		
INCHES .X ± .10 .XX ± .020 .XXX ± .015	HOLES Ø.X ± .10 Ø.XX ± .015 Ø.XXX ± .010		TITLE UNIVERSAL SERIAL BUS, SINGLE PORT VERTICAL, PCB, 30u" SEL GOLD PLATED		
APPROVALS		DATE	SIZE X	PART NO. USB-B-S-VT-30	REV. A
DRAWN	AY	8/18/11			
CHECKED	AL	8/18/11			
APPROVED			REF: S00005C	SCALE: NTS	SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[USB-B-S-VT-30](#)