


APPROVED: _____

DATE: _____ TITLE: _____

| Rev | AWO # | Description | Date | Appr |
|-----|-------|-----------------|---------|-------|
| - | | RELEASED | 12/3/04 | |
| A | | REDRAWN | 6/8/11 | |
| B | | UPDATED DRAWING | 9/14/17 | HR/TY |



SPECIFICATIONS:

Material:

Insulator: PBT, Glass filled, rated UL 94V-0

Insulator color: White

Contacts: Phosphor Bronze

Shell: Copper Alloy, nickel plated

Plating:

Gold flash over Nickel underplate on contact area,

Tin over Copper underplate on PCB tails

Electrical:

Voltage rating: 30 VAC

Current rating: 1.5 Amp

Contact resistance: 30 mohms max.

Insulation resistance: 1000 Mohms min.

Dielectric withstanding voltage: 500 VAC

Temperature Rating:

Operating temperature: -20°C to +60°C

Environmental:

Lead free, RoHS compliant.



| | | | | | |
|--|----|---------|---|---------------|------|
| UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES .X ± .10 Ø.X ± .10 .XX ± .020 Ø.XX ± .015 .XXX ± .015 Ø.XXX ± .010 | | | ADAM TECH 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710 | | |
| APPROVALS | | | TITLE | | |
| DATE | | | UNIVERSAL SERIAL BUS | | |
| DRAWN | SS | 10/4/04 | SINGLE PORT, VERTICAL, PCB | | |
| CHECKED | | | SIZE | PART NO. | REV. |
| APPROVED | | | X | USB-B-S-VT-WT | B |
| REF: S00005C | | | SCALE: NTS | SHEET 1 OF 1 | |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[USB-B-S-VT-WT](#)