






APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	1/22/21	
A		UPDATE TITLE	6/27/24	WX/RC



SPECIFICATIONS:

Material:

Insulator: Thermoplastic, rated UL 94V-0

Insulator color: Black

Contacts: Brass

Shell: Stainless Steel

Plating:

30u" Palladium Gold over Nickel underplate on contact area,

Tin over Nickel underplate on solder tails

Electrical:

Voltage rating: 20 V

Current rating: 5 Amps max

Insulation resistance: 100 Mohms min @100 VDC

Dielectric withstanding voltage: 100 VAC for 1 Minute

Temperature Rating:

-40°C to +105°C

Environmental:

Lead free, RoHS compliant.




PACKAGED ON TAPE & REEL

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE MILLIMETERS. TOLERANCES: EXCEPT AS NOTED			ADAM TECH		909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710	
X	MM	ANGLE				
.X	± 0.50	± 5°				
.XX	± 0.30					
	± 0.20					
DRAWN	LH	1/22/21	TITLE UNIVERSAL SERIAL BUS, TYPE C, FEMALE, TRANSMISSION EFFICIENCY: Gen2 10Gbps RIGHT ANGLE, BLACK INSULATOR			
CHECKED	RC	1/22/21				
APPROVED						
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY AND SHOULD NOT BE USED WITHOUT PRIOR WRITTEN PERMISSION FROM ADAM TECH			SIZE X	PART NO. USB-C32-S-RA-CS27A-BK-30-X-T/R	REV. A	
			REF: S00013T	SCALE: NTS	SHEET 1 OF 2	

APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
SEE SHT 1 OF 2 FOR REVISION				



RECOMMENDED PCB LAYOUT
PCB Thickness=1.0 For 1.50 Solder Tail
PCB Thickness=1.6 For 1.90 Solder Tail

USB TYPE -C Pin Assignments

Pin Number	Signal Name	Pin Number	Signal Name
A1	GND	B12	GND
A2	SSTXp1	B11	SSRXp1
A3	SSTXn1	B10	SSRXn1
A4	VBUS	B9	VBUS
A5	CC1	B8	SBU2
A6	Dp1	B7	Dn2
A7	Dn1	B6	Dp2
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
A10	SSRXn2	B3	SSTXn2
A11	SSRXp2	B2	SSTXp2
A12	GND	B1	GND

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS
ARE MILLIMETERS. TOLERANCES: EXCEPT AS NOTED

	MM	ANGLE
X	± 0.50	± 5°
.X	± 0.30	
.XX	± 0.20	

DRAWN	LH	1/22/21
CHECKED	RC	1/22/21
APPROVED		

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY
AND SHOULD NOT BE USED WITHOUT PRIOR WRITTEN
PERMISSION FROM ADAM TECH

ADAM
TECH

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE UNIVERSAL SERIAL BUS, TYPE C, FEMALE,
TRANSMISSION EFFICIENCY: Gen2 10Gbps
RIGHT ANGLE, BLACK INSULATOR

SIZE X	PART NO. USB-C32-S-RA-CS27A-BK-30-X-T/R	REV. A
REF: S00013T	SCALE: NTS	SHEET 2 OF 2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[USB-C32-S-RA-CS27A-BK-30-B-TR](#)