







1.0mm Pitch

SERIES

6226

1.0mmピッチ NON-ZIF ストレート SMT 両面接点
1.0mmPitch LIF Vertical SMT Dual-sided contact

SECT. X-X

基板取付け寸法 (コネクタ搭載面側)
MOUNTING LAYOUT (CONN. MOUNTING SIDE)

適用FPC/FFC

APPLICABLE FPC/FFC

	公差 TOLERANCE		
	P	W	M
FPC	±0.02	+0.07 -0.05	±0.05
FFC	±0.05	±0.03	±0.1

寸法表 DIMENSION				
型番 P/N	極数 No. of Pos.	A	B	
00 6226 004 00X 800 X	4	3	6.3	
↑ 005	5	4	7.3	
006	6	5	8.3	
007	7	6	9.3	
008	8	7	10.3	
009	9	8	11.3	
010	10	9	12.3	
011	11	10	13.3	
012	12	11	14.3	
013	13	12	15.3	
014	14	13	16.3	
015	15	14	17.3	
016	16	15	18.3	
017	17	16	19.3	
018	18	17	20.3	
019	19	18	21.3	
↓ 00 6226 020 00X 800 X	20	19	22.3	


生産対応可能極数については、営業部にご確認願います。
Feel free to contact our sales department for
available numbers of positions.

注文コード ORDERING CODE

00 6226 0XX 00X 800 X

00: トレー梱包
TRAY PACKAGE極数
NUMBER
OF
POSITIONS800+: スズ銅めっき Sn-Cu Plated (RoHS対応品 RoHS Compliant Product)
800: スズ鉛めっき Sn-Pb Plated1: 自然色 Natural color
2: 黒 Black color
3: 灰 Gray color

SERIES



型 番 P/N	極 數 NO. OF POS.	A	B
04 6226 017 40X 800 X	17	19.7	21.7
04 6226 018 40X 800 X	18	20.7	22.7
04 6226 020 40X 800 X	20	22.7	24.7

注文コード ORDERING CODE

梱包数量 1000個/リール
PACKING QUANTITY : 1000/Reel

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kyocera AVX:](#)

[046226007201800+](#) [046226010302800+](#) [046226020402800+](#) [046226017301800+](#) [046226017302800+](#)
[046226017401800+](#) [046226017402800+](#) [046226018301800+](#) [046226018303800+](#) [046226015301800+](#)
[046226016302800+](#)