


| Unless otherwise specified dimensional tolerance as follows: | |
|--|---------------|
| DIMENSION (mm) | TOLERANCE ±mm |
| 1-16 | 0.1 |
| 16.1-63 | 0.2 |
| 63.1-250 | 0.3 |
| 250.1-1000 | 0.5 |



| A | B | C | D |
|---------|--------|---------|---------|
| HAF-10L | 14.4mm | 106.7mm | 116.8mm |
| HAH-10L | 0.0mm | 48.3mm | 57.9mm |

(unit : mm)

| TITLE | HAF-10L HAH-10L |
|----------------------|--------------------|
| DENSEI-LAMBDA | |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TDK-Lambda:](#)

[HAF10L](#)