

2500W 1U Front End Power Supplies

Features

- ◆ 1U rackmount containing up to 4 units
- ◆ Internal ORing MOSFET & Current Share
- ◆ High Efficiency
- ◆ Up to 9,500W in 1U rack
- ◆ PMBus™(I²C) and LAN options



Key Market Segments & Applications



(HFE2500-48 model)

Specifications

Model		
Input Voltage Range (2)	VAC	85 - 265VAC, 47 - 63Hz. See model selector for power derating
Input Current (Max) 100/230VAC	A	15 / 12A
Inrush Current	A	<50A
Power Factor Correction	-	Meets EN61000-3-2, PF > 0.98 at full load
Temperature Coefficient	%/°C	<0.02%/°C
Overcurrent Protection	%	105 - 115%
Overvoltage Protection (1)	%	110% (Tracking). Cycle AC to reset or utilize Remote On/Off
Overtemperature Protection (1)	-	Shutdown with automatic reset. Warning signal provided
Hold-up time	ms	>10ms, 115/230VAC Input, 80% loading
Leakage Current	mA	< 0.75 / 1.5mA, 100 / 230VAC, 60Hz
Remote Sense Compensation	-	HFE2500-12: 0.25V / Wire, HFE2500-24: 0.5V / Wire, HFE2500-48: 1V / Wire
Indicators	-	AC OK: Green LED, DC OK / Fail: Green / Red LED
Remote On/Off	-	Unit ON: 0 - 0.6V or short, OFF: 2 - 15V or open circuit
Parallel Operation (1)	-	Yes, single wire current share, up to 95% accuracy (load dependant), up to 8 units
AC Fail Signal	-	Open Collector, ON when AC is within 85 - 270VAC
DC Good Signal	-	Open Collector, ON when output is above 85 to 95% of setpoint (tracking)
Remote Adjust (1)	-	By either external 0 - 5V signal or 1k potentiometer
I ² C Interface (1)	-	Isolated from output, Add suffix /S, PMBus compatible
Auxiliary Output	-	11.2 - 12.5V, 0.5A, 240mV ripple and noise
Operating Temperature	°C	-10 to +70°C, derate 2%/°C from 50 to 60°C, 2.5%/°C from 60 to 70°C
Storage Temperature	°C	-30 to +85°C
Humidity (Non condensing)	%RH	Operating: 10 - 90%RH, Storage: 10 - 95%RH
Cooling	-	Two variable speed internal fans, airflow exits across input/output connector (3)
Withstand Voltage	-	I/P to O/P 3kVAC, I/P to GND 2kVAC, O/P to GND: HFE2500-12, -24V 500VAC, HFE2500-48 2250 VDC 1min, (POE)
Isolation Resistance	MΩ	>100MΩ at 25°C & 70%RH, Output to Ground 500VDC
Vibration (Basic transportation)	-	Meets IEC60068-2-64
Shock (Basic transportation)	-	Meets IEC60068-2-27
Safety Agency Certifications	-	UL60950-1, EN60950-1, CE Mark
Conducted and Radiated EMI	-	EN55032 & FCC part 15; Conducted class B, Radiated class A
Immunity	-	IEC61000-4-2 (lv 2,3), -3 (lv 2), -4 (lv 2), -5 (lv 3,4), -6 (lv 4), -8 (lv 4), -11
Size (W x H x D)	in	Power Supply: 4.21 x 1.61 x 12.8", Rack: 17.5 x 1.72 x 15.8"
Weight	g	Power Supply: 2100g, Rack: 5000g
Warranty	yrs	Three Years

(1) See installation manual for detailed specifications & test methods

(2) Derate linearly 1.3%/V from 100VAC to 85VAC input

(3) Reverse air - contact factory

Model Selector


Model	Output Voltage	Adjust Range ⁽¹⁾	Max Current (Vin>180VAC)	Max Power (Vin>180VAC)	Max Current (100<Vin<132VAC) ⁽²⁾	Max Power (100<Vin<132VAC) ⁽²⁾
HFE2500-12	12V	9.6 - 13.2V	200A	2400W	125A	1500W
HFE2500-12/S	12V	9.6 - 13.2V	200A	2400W	125A	1500W
HFE2500-24	24V	19.2 - 29V	104A	2496W	62.5A	1500W
HFE2500-24/S	24V	19.2 - 29V	104A	2496W	62.5A	1500W
HFE2500-48	48V	38.4 - 58V	52A	2496W	31.25A	1500W
HFE2500-48/S	48V	38.4 - 58V	52A	2496W	31.25A	1500W
Model	Load Reg	Line Reg	Ripple & Noise ⁽¹⁾	Efficiency (%) ⁽⁴⁾	PMBus/ I ² C	
HFE2500-12	60mV	30mV	240mV	90 / 92%	-	
HFE2500-12/S	60mV	30mV	240mV	90 / 92%	Yes	
HFE2500-24	120mV	60mV	240mV	90 / 92%	-	
HFE2500-24/S	120mV	60mV	240mV	90 / 92%	Yes	
HFE2500-48	240mV	120mV	480mV	91 / 93%	-	
HFE2500-48/S	240mV	120mV	480mV	91 / 93%	Yes	

(4) At 75% load, 100 / 230VAC input

Accessories

Model	Description	Maximum Rack Current
HFE2500-S1U	Four slot 19" rack, IEC320-C20 input connector	320A each side (640A total)
HFE2500-S1U-TB	Four slot 19" rack, Terminal Block input connector	320A each side (640A total)
HFE2500/BP	One slot blanking panel, two provided with each rack	-
HFE2500-LAN	Plug in LAN module. Takes up one rack slot. For use with /S models only.	-

Outline HFE2500S1U



For Additional Information, please visit
<https://product.tdk.com/info/en/products/power/index.html>



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TDK-Lambda:](#)

[HFE2500-12](#) [HFE2500-24](#) [HFE2500-48](#) [HFE2500-S1U](#) [HFE2500-S1U-TB](#) [HFE2500-48/S](#) [HFE2500-12/S](#)
[HFE2500/BP](#) [HFE2500-24/S](#) [HFE2500LAN](#)