

## Rack

### ■ Index

Category	Series/Model	Part Number	Explanation
19 inch rack mounted kit	Genesys Series (Only GENH Model)	GENH/RM	To install one GENH750W unit or two units side-by-side in a standard 19 inch rack in 1U (1.75 inch) height
Blank panel	Z+	Z-BP	In cases where the entire rack is not occupied with power units, this blank panels can be installed. *Z-BP for 70mm
	Z+	Z-WBP	In cases where the entire rack is not occupied with power units, this blank panels can be installed. *Z-WBP for 105mm
Housing rack	Z+	Z-NL100	Six units (70mm) can be assembled into 19-Inch rack/2U high. Or four units (105mm) can be assembled into 19-Inch rack/2U high to meet your configuration requirements.
	Z+	Z-NL200	Dual Output Housing (for 105mm) or Triple Output Housing (for 70mm) *Same P/N for both Dual & Triple Output Housing
Shelf rack	FPS1000 (Standard type or /S option)	FPS-S1U	Rack (3 slot) , contains two blanking panels.
	FPS1000 (/P or /PS option)	FPS-S1U/P	Rack (3 slot) , contains two blanking panels.
	HFE1600	HFE1600-S1U	Five slot 19 inch rack, IEC320-C16 input connectors
		HFE1600-S1U-TB	Five slot 19 inch rack, terminal block
	HFE2500	HFE2500-S1U	Four slot 19 inch rack, IEC320-C20 input connector
		HFE2500-S1U-TB	Four slot 19 inch rack, terminal block

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## TDK-Lambda:

[HFE1600-S1U](#) [HFE1600-S1U-TB](#) [HFE2500-S1U](#) [HFE2500-S1U-TB](#) [Z-NL200](#) [Z-WBP](#) [Z-BP](#) [GENH/RM](#)  
[ZUP/NL101](#) [ZUP/NL100](#) [ZUP/NL200](#) [HFE1600-D1U-TB](#) [HFE1600-D1U](#) [Z-NL100](#) [HFE2500-LAN](#) [HFE1600-LAN](#)  
[FPS-S1U](#) [FPS-S1U/P](#) [FPS-T1U](#) [FPS-T1U/P](#) [HFE1600-BP](#) [HFE2500-BP](#)