


Tripp Lite Waber Industrial Power Strip, 6-Outlet, 6 ft. (1.83 m) Cord

MODEL NUMBER: **6SP**



Highlights

- 6 outlets
- 6-ft. (1.83 m) cord
- 13.7-in. overall length
- Lighted master power switch

Package Includes

- 6SP Power Strip
- Warranty information
- Instruction manual

Description

The Waber-by-Tripp Lite 6SP Power Strip offers a convenient method of power distribution in workbench, wallmount or floor mount applications. Includes 6 NEMA 5-15R output receptacles with 1.625 inch center-to-center spacing, 6-ft. (1.83 m) AC line cord and keyhole mounting tabs for installation in a wide variety of applications. Corded, multi-outlet strip reduces cable clutter and enables the connection of multiple electrical devices to a single AC wall socket. Unfiltered electrical pass-through makes 6SP ideal for distributing alternate waveform UPS or generator power. Features rugged all-metal housing, lighted power switch, 15A resettable circuit breaker and attractive blue/gray color scheme. PLUG/OUTLETS - Input: NEMA 5-15P/Output: 6 NEMA 5-15R ELECTRICAL - 120V AC, 50/60Hz, 15A (Requires standard NEMA 5-15R wall receptacle) FORMAT - Corded power distribution strip

Features

- Multi-outlet power strip offers convenient power distribution in workbench, wallmount or floor mount applications
- Includes 6 NEMA 5-15R output receptacles with 1.625-in. center-to-center outlet spacing
- Lighted power switch
- Keyhole mounting tabs for installation in a wide variety of applications
- UL1363 (USA), cUL (Canada)
- 15A power handling capacity with circuit breaker
- 6-ft. (1.83 m) AC line cord

Specifications

OVERVIEW

UPC Code	037332103383
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	15A 120V
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	6
Input Cord Length (m)	1.83
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	1800
Output Receptacles	(6) 5-15R
Circuit Breaker (amps)	15
Transformer Accommodation	(2) Yes
Outlet Orientation	Single row of 6
Right-Angle Outlets	No
Outlet Spacing	1.625 in.
USER INTERFACE, ALERTS & CONTROLS	
Switches	Illuminated 2-position switch controls power to all outlets
PHYSICAL	
Color	Gray
Antimicrobial Coating	No
Power Cord Color	Black
Housing Color	Blue; Gray
Integrated Keyhole Mounting Slots	Yes (Includes flanges)
Keyhole Slot Mounting Measurement (Center to Center)	Distance between keyhole tabs = 261.92mm; Distance between end tabs = 330.17mm
Material of Construction	Metal
Outlets Measurement (Center to Center)	41.3mm
Receptacle Color	Black
Shipping Dimensions (hwd / cm)	36.83 x 9.14 x 15.49
Shipping Dimensions (hwd / in.)	14.50 x 3.60 x 6.10



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Shipping Weight (kg)	1.01
Shipping Weight (lbs.)	2.22
Unit Dimensions (hwd / cm)	31.75 x 6.35 x 3.8
Unit Dimensions (hwd / in.)	12.5 x 2.5 x 1.5
STANDARDS & COMPLIANCE	
Canada	cUL
UL1363 (Power Tap)	UL1363
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite](#):

[6SP](#)