

RG59 Coax Cable with F-Type Connectors, 25 ft. (7.62 m)

MODEL NUMBER: **A200-025**



Highlights

- Double Shielded RG59 Coax
- Gold Plated screw type F connectors
- Fully molded ends ensure long life use

Package Includes

RG59 Coax cable with F-Type Connectors - 25-ft. (7.62 m)

Features

- Double Shielded (Foil and Braid) RG59B/U Cable
- 24K Gold Plated screw type F connectors
- Fully molded ends ensure long life use
- Use with Cable or Satellite Receivers, VCR, DVD, Coax enabled TV

Specifications

OVERVIEW	
UPC Code	037332146656
Product Type	Passive
Technology	Coax; RG59/RG6
PHYSICAL	
Color	Black
Cable Length (ft.)	25
Cable Length (m)	7.6
Shipping Dimensions (hwd / cm)	30.48 x 25.40 x 0.25
Shipping Dimensions (hwd / in.)	12.00 x 10.00 x 0.10
Shipping Weight (kg)	0.34
Shipping Weight (lbs.)	0.75



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

CONNECTIONS	
Side A - Connector 1	F-TYPE (MALE) THREADED COAX
Side B - Connector 1	F-TYPE (MALE) THREADED COAX
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[A200-025](#)