

230V Automatic Voltage Switch with Surge Protection, 190 Joules, Direct Plug-In

MODEL NUMBER: AVS5D



Highlights

- Direct plug-in / 1 outlet
- Over- and undervoltage protection
- Surge and spike protection
- 5-amp current rating

Package Includes

- AVS5D Automatic Voltage Switch
- Owner's Manual

Description

AVS5D Automatic Voltage Switch is a power protection device combining overvoltage, undervoltage and spike/surge protection for your appliances and electronics. This device also guards against surges and spikes that may occur when power is restored. The AVS5D easily handles small refrigerators, small freezers, small air conditioners, TVs and computer equipment, plugged into its single outlet, from fluctuating power.

Program buttons let you quickly set voltage range, on/off delay, overload protection and digital display mode. The easy-to-read digital LED displays show you voltage, wattage, settings and status at a glance. The AVS5D features surge-protecting components to guard against spikes and surges.

Features

- 5-amp current rating
- BS 1363 UK plug
- BS 1363 UK outlet
- Program buttons
- Voltage LED
- Load LED
- Digital LED display

Specifications

OVERVIEW	
UPC Code	037332182197
INPUT	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Nominal Input Voltage(s) Supported	220V AC
Recommended Electrical Service	230V
Voltage Compatibility (VAC)	230
Maximum Surge Amps	4500kA
Input Plug Type	BS1363
Input Cord Details	Direct Plug-In
Input Cord Length (ft.)	0
Right-Angle Plug	No
Input Cord Length (m)	0.00
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(1) British BS 1363A
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	190
AC Suppression Response Time	<1ns
Automatic Shut-Off	No
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection	No
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
PHYSICAL	
Color	Light Gray
Antimicrobial Coating	No
Housing Color	Light Gray
Integrated Keyhole Mounting Slots	No
Material of Construction	Plastic
Receptacle Color	White
Shipping Dimensions (hwd / cm)	13.49 x 8.59 x 6.60



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Shipping Dimensions (hwd / in.)	5.31 x 3.38 x 2.60
Shipping Weight (kg)	0.18
Shipping Weight (lbs.)	0.40
Unit Dimensions (hwd / cm)	13.21 x 6.40 x 4.78
Unit Dimensions (hwd / in.)	5.20 x 2.52 x 1.88
SPECIAL FEATURES	
Rotatable Outlets	No
STANDARDS & COMPLIANCE	
Certifications	CE
Approvals	RoHS

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[AVS5D](#)