

## 8-Port 1U Rack-Mount USB/PS2 KVM Switch with On-Screen Display

MODEL NUMBER: **B042-008**



### Description

Tripp Lite's NetController 8-Port, 1U rackmount KVM Switch is an affordable, highly-flexible enterprise class KVM Switch, which allows the user to connect either USB or PS/2 keyboards and mice. In addition, P780-Series USB/PS2 combo KVM cable kits allow you to connect either USB or PS/2 computers, without the need to purchase separate cables or adapters. Control up to 8 directly connected computers, or expand the number of connected computers to up to 248 by daisy chaining up to 15 additional B042-Series KVM switches. Switch between connected computers via the On-Screen Display (OSD), pushbuttons, or keyboard hotkey commands. Other features include: password protection, auto-scanning, auto-logout, firmware upgrade and video support up to 2048 x 1536 (QXGA). Mounts easily in a standard 19" rack/cabinet and includes all necessary mounting hardware. Compatible with all major operating systems. Constructed of heavy-duty steel housing.

### Features

- NetController 8-Port, 1U rackmount KVM switch
- Control 8 computers via a single VGA monitor and USB or PS/2 keyboard/mouse
- P780-Series USB/PS2 combo KVM cable kits allow you to connect either USB or PS/2 computers, without the need to purchase separate cables or adapters
- Control up to 248 computers by daisy chaining up to 15 additional B042-Series KVM switches
- Allows for easy customization of ports by daisy-chaining any combination of B042-Series KVM's (4-, 8- or 16-port)
- Standard 19" Rackmount size - hardware included
- On-Screen Display (OSD) menu for intuitive operation and easy control
- Switch between connected computers via the On-Screen Display (OSD), pushbuttons, or keyboard hotkey commands
- Supports video resolution up to 2048 x 1536

### Highlights

- NetController 8-Port, 1U rackmount KVM switch
- Control 8 computers via a single VGA monitor and USB or PS/2 keyboard/mouse
- Control up to 248 computers by daisy chaining up to 15 additional B042-Series KVM switches
- P780-Series USB/PS2 combo KVM cables kits allow you to connect either USB or PS/2 computers, without the need to purchase separate cables or adapters
- Compatible with all major operating systems

### Package Includes

- B042-008 NetController 8-Port, 1U rackmount KVM switch
- External Power Supply with NEMA 1-15P Plug (Input: 100-240V, 50/60Hz, 0.5A / Output: 9V, 1A)
- Rackmount hardware
- 8 In. Daisychain cable ( for longer daisy-chain cables, see Tripp Lite P781 series cables)
- Daisychain terminator
- 4 ft. HD15 to DB9 firmware upgrade cable
- CD with owner's manual and quick start guide
- Quick start guide



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

- Password protection and auto-logout features
- Firmware upgradeable
- Robust metal case design ensures best EMI/RFI shielding and video quality
- Hot-swappable: disconnect and reconnect USB computers without rebooting
- Supports standard 5-button Microsoft, Logitech, or comparable mice
- Supports standard Microsoft, Logitech, or comparable keyboards
- Compatible with all major operating systems
- Constructed of heavy-duty steel housing

## Specifications

OVERVIEW	
UPC Code	037332141392
AC Adapter	Input: 100-240V, 50/60Hz, 1.0A / Output: 9V, 1.33A
Console	No
Max CPU	248
Technology	PS/2; USB; VGA/SVGA
VIDEO	
Max Supported Video Resolution	2048 x 1536 @60Hz
Max. Distance (Between any 2 Units)	98ft (30m)
Max Number of Ports (Entire Chain)	248
INPUT	
Voltage Compatibility (VAC)	100; 110; 120; 127; 200; 208; 220; 230; 240
External Power Supply Plug(s)	NEMA 1-15P North America
POWER	
External Power Supply Input Specs (V / Hz / A)	100-240V / 50/60Hz / 1.0A
External Power Supply Output Specs (V / A)	9V/ 1.33A
External Power Supply Cord Length (ft.)	5
External Power Supply DC Barrel Connector Specs	OD: 5.5 x 2.1 x 9.5mm, Positive Pin, Negative Sleeve
External Power Supply Certifications	FCC; UL; cUL; TUV; CB
USER INTERFACE, ALERTS & CONTROLS	



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

LED Indicators	Red (Link); Green (Selected PC)
<b>PHYSICAL</b>	
Color	Black
Material of Construction	Steel
Rackmountable	Yes
Shipping Dimensions (hwd / cm)	7.11 x 28.19 x 43.43
Shipping Dimensions (hwd / in.)	2.80 x 11.10 x 17.10
Shipping Weight (kg)	2.77
Shipping Weight (lbs.)	6.10
Unit Dimensions (hwd / in.)	1.8 x 16.1 x 6.5
Unit Packaging Type	Box
Unit Weight (kg)	1.81
Unit Weight (lbs.)	4.00
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	32 to 104 F (0 to 40 C)
Storage Temperature Range	-4 to 140 F (-20 to 60 C)
Relative Humidity	0%-90% RH, Non-Condensing
BTUs	21.8 BTU/Hr
Power Consumption (Watts)	6.4
<b>COMMUNICATIONS</b>	
IP Remote Access	No
<b>CONNECTIONS</b>	
Ports	8
PC/Server Connections	PS/2; USB; VGA
Side A - Connector 1	(8) HD15 (FEMALE)
Side B - Connector 1	(2) HD15 (FEMALE)
Side B - Connector 2	HD15 (MALE)
Side B - Connector 3	(2) MINI DIN-6 (FEMALE)
Side B - Connector 4	(2) USB A (FEMALE)
Computer Keyboard and Mouse Interface	PS/2; USB
Computer Monitor Interface	VGA
Console Keyboard and Mouse Interface	PS/2; USB



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Console Monitor Interface	VGA
Connector Plating	Nickel
<b>FEATURES &amp; SPECIFICATIONS</b>	
Number of Users	1
NIAP-Certified Secure	No
On-Screen Display (OSD)	Yes
Port Selection	Pushbutton; Hotkey; OSD
Driver Required	No
Cat5 KVM Switch	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Certifications	Tested to CE, FCC, RoHS, REACH
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[B042-008](#)