

NetCommander 8-Port Cat5 KVM Switch 1U Rack-Mount with PS2 to USB Input Adapter

MODEL NUMBER: **B072-008-1A**



Features

- Expandable - Cascade a second level of KVM switches to control up to 128 servers from a single station
- Extend distance: between computer and switch up to 30 meters/100 ft.
- Rack mountable: sleek, 1U space saving KVM switches
- Accepts PS2 Mouse and Keyboard (or USB Mouse and Keyboard with included adapter)
- Innovative CAT5 technology: eliminate cable clutter at the rack
- Multi-layer security: protects your corporate data
- Easy server management: choice of On Screen Display, Hot-key, or push button control
- Multi-platform: PS/2 and USB support
- To convert DisplayPort or HDMI computers to VGA, use Tripp Lite adapters P134-06N-VGA-V2 or P131-06N. Maximum video resolutions using adapters may vary.
- Easily add IP functionality with Tripp Lite Model B051-000
- Add Tripp Lite Model B021-000-19 for space saving, in-the-rack, LCD, Keyboard and Mouse
- Compact Size: 17"W x 5"D x 1.75"H
- Video Resolution: 1600x1200@75Hz
- Internal Power Supply
- Compatible with all major operating systems
- Constructed of heavy-duty steel housing

Specifications

Highlights

- 8 RJ45 Ports utilize inexpensive Cat5 patch cables
- Expandable - Cascade a second level of KVM switches to control up to 128 servers from a single station
- Accepts PS2 or USB Mouse and Keyboards with included Adapter

System Requirements

- Computers: The Tripp Lite B078-101-USB-1 Server Interface Module must be used to connect a server to the server ports on the KVM switch.
- For computers with Displayport or HDMI, change to VGA using Tripp Lite adapters P134-06N-VGA-V2 or P131-06N. Maximum video resolutions using adapters may vary.
- Compatible with all major operating systems

Package Includes

- 8-Port NetCommander 1U Rackmount Cat5 KVM Switch
- PS2 to USB Adapter
- 6-ft. (1.83 m) Power Cord
- 6-ft. (1.83 m) Firmware Upgrade Cable
- Rackmount Bracket kit



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

OVERVIEW	
UPC Code	037332186584
Max CPU	128
Technology	Cat5/5e; PS/2; USB; VGA/SVGA
VIDEO	
Max Supported Video Resolution	1600 X 1200 @ 75 Hz
Max. Distance (Between any 2 Units)	100 ft (30.5m)
Max Number of Ports (Entire Chain)	128
INPUT	
Voltage Compatibility (VAC)	100; 110; 120; 127; 200; 208; 220; 230; 240
Input Frequency	50/60Hz
Input Current	120V (0.7A) / 230V (0.3A)
Power Input Receptacle	IEC-320-C14
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	Green(CPU ON, SELECTED)
PHYSICAL	
Color	Black
Material of Construction	Steel (Steel, Electrogalvanized, Cold Rolled, Coil)
Rackmountable	Yes
Shipping Dimensions (hwd / cm)	11.00 x 51.51 x 19.51
Shipping Dimensions (hwd / in.)	4.33 x 20.28 x 7.68
Shipping Weight (kg)	2.42
Shipping Weight (lbs.)	5.34
Unit Dimensions (hwd / in.)	1.7 x 4.8 x 16.8
Unit Packaging Type	Box
Unit Weight (kg)	1.59
Unit Weight (lbs.)	3.50
ENVIRONMENTAL	
Operating Temperature Range	32 to 104 F (0 to 40 C)
Storage Temperature Range	-40 to 158 F (-40 to 70 C)
Relative Humidity	0% to 80% RH, Non-Condensing



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

BTUs	27.3 BTU/Hr
Power Consumption (Watts)	8
COMMUNICATIONS	
IP Remote Access	No
CONNECTIONS	
Ports	8
PC/Server Connections	PS/2; USB; VGA
Side A - Connector 1	HD15 (FEMALE)
Side A - Connector 2	(2) MINI DIN-6 (FEMALE)
Side A - Connector 3	RJ11 (FEMALE)
Side B - Connector 1	(8) RJ45 (FEMALE)
Computer Keyboard and Mouse Interface	PS/2; USB
Computer Monitor Interface	VGA
Console Keyboard and Mouse Interface	PS/2
Console Monitor Interface	VGA
FEATURES & SPECIFICATIONS	
Number of Users	1
NIAP-Certified Secure	No
On-Screen Display (OSD)	Yes
Port Selection	Pushbutton; Hotkey; OSD
Driver Required	No
Cat5 KVM Switch	Yes
Recommended Category Cable	Cat5e/6 Cables
STANDARDS & COMPLIANCE	
Certifications	Tested to UL 60950-1 (USA), CAN/CSA (Canada), FCC Part 15 Class A, CE, IEC 60950-1, RoHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[B072-008-1A](#)