

## 4-Port HDMI Splitter for Video and Audio, 1920x1200 at 60Hz/1080p (HDMI F/4xF)

MODEL NUMBER: **B118-004**



Transmit a HDMI signal from a single source to four displays

### Description

Tripp Lite's B118-004, 4-Port HDMI Splitter allows the digital signal from a Blu-Ray player or other HDMI device to be displayed on four HDMI displays. Connect a DVI-D Single Link display using an HDMI to DVI adapter, such as Tripp Lite's P566-Series cables. Installation is quick and simple, with no software or drivers to install. Locate your HDMI source up to 13 ft. (4 m.) from the splitter, and the splitter up to 16 ft. (5 m.) from a display, for a max distance of 29 ft. (9 m.) between source and display. Multiple splitters can be cascaded together to connect additional monitors, with no more than 6 levels of splitters in all. Supports HD video resolutions up to 1080p, and computer video resolutions up to 1920 x 1200. High Speed HDMI v1.4 and 3D compliant, with support for 36-bit Deep Color (12-bits per channel). Supports DTS-HD, Dolby True HD and 7.1 Channel Surround Sound audio. HDCP v1.4 and EDID compliant.

### Features

- Transmit a HDMI signal from a single source to four displays
- Display HD video resolutions up to 1080p, and computer video resolutions up to 1920 x 1200
- Supports up to 36-bit Deep Color (12-bits per channel)
- High Speed HDMI v1.4 and 3D compliant
- Supports DTS-HD, Dolby True HD and 7.1 Channel Surround Sound audio
- HDCP v1.4 and EDID compliant
- Plug and play; No software or drivers required
- Locate a monitor up to 29 ft. (9 m.) from a HDMI source; up to 13 ft. (4 m.) between the source and the switch; up to 16 ft. (5 m.) between the switch and a monitor
- Cascade multiple levels of splitters together to increase the number of connected monitors, with no more than 6 levels of splitters in all
- Connect a DVI-D Single Link display using an HDMI to DVI adapter, such as Tripp Lite's P566-Series

### Highlights

- Display HD video resolutions up to 1080p, and computer video resolutions up to 1920 x 1200
- Supports up to 36-bit Deep Color (12-bits per channel)
- High Speed HDMI v1.4 and 3D compliant
- Supports DTS-HD, Dolby True HD and 7.1 Channel Surround Sound audio
- HDCP v1.4 and EDID compliant
- Plug and play; No software or drivers required

### System Requirements

- TV's with an available HDMI port and a HDMI peripheral device (e.g. Blu-Ray player, DVR, etc.)
- The cable connecting the HDMI source to the splitter must be no longer than 13 ft. (4 m.)
- The cable connecting the splitter to a HDMI monitor must be no longer than 16 ft. (5 m.)

### Package Includes

- B118-004 4-Port HDMI Splitter
- External Power Supply with NEMA 1-15P Plug( Input: 100-240V, 50/60Hz, 0.5A; Output: 5V, 1.2A, 4.9 ft. )
- Owners Manual



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

cables

## Specifications

OVERVIEW	
UPC Code	037332181107
Technology	HDMI
VIDEO	
Max Supported Video Resolution	1080p @60Hz
Max. Distance (Between any 2 Units)	16ft (5m)
Max Number of Ports (Entire Chain)	4096
Max Supported Color Depth	12-bit
3D Video Supported	Yes
AUDIO	
Audio Specification	7.1 Surround Sound, Dolby True HD, DTS-HD, DSD
INPUT	
Voltage Compatibility (VAC)	100; 110; 120; 127; 200; 208; 220; 230; 240
External Power Supply Plug(s)	NEMA 1-15P North America
POWER	
External Power Supply Input Specs (V / Hz / A)	100-240V / 50/60Hz / 0.8A
External Power Supply Output Specs (V / A)	5V / 2A
External Power Supply Cord Length (ft.)	5
External Power Supply Cord Length (m.)	1.5
External Power Supply DC Barrel Connector Specs	OD: 5.5 x 2.1 x 10mm, Positive Pin, Negative Sleeve
External Power Supply Certifications	CE; FCC; UL; RoHS
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	Green (Input, Output 1, Output 2, Output 3, Output 4)
PHYSICAL	



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Color	Black
Material of Construction	Steel
Shipping Dimensions (hwd / cm)	5.33 x 14.22 x 20.32
Shipping Dimensions (hwd / in.)	2.10 x 5.60 x 8.00
Shipping Weight (kg)	0.45
Shipping Weight (lbs.)	1.00
Unit Dimensions (hwd / cm)	2.4 x 11.1 x 7.5
Unit Dimensions (hwd / in.)	0.9 x 4.4 x 3
Unit Packaging Type	Box
Unit Weight (kg)	0.23
Unit Weight (lbs.)	0.5
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	32 to 104 F (0 to 40 C)
Storage Temperature Range	-4 to 158 F (-20 to 70 C)
Relative Humidity	5% to 90% RH, Non-Condensing
BTUs	34.1 BTU/Hr
Power Consumption (Watts)	10
<b>COMMUNICATIONS</b>	
Signal Range (ft.)	16
Signal Range (m)	5
EDID Compatible	Yes
Consumer Electronics Control (CEC) Supported	Yes
Latency	80ms
<b>CONNECTIONS</b>	
Ports	4
Side A - Connector 1	HDMI (FEMALE)
Side B - Connector 1	(4) HDMI (FEMALE)
Connector Plating	Gold
<b>FEATURES &amp; SPECIFICATIONS</b>	
HDCP Specification	1.4
Driver Required	No
<b>STANDARDS &amp; COMPLIANCE</b>	



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Certifications	Tested to CE, FCC, RoHS, REACH
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[B118-004](#)