

VGA with Audio over Cat5/Cat6 Extender Kit, Transmitter & Receiver with EDID, 2 Local/2 Remote Displays, 1440x900, Up to 500 ft. (152 m)

MODEL NUMBER: **B130-202A**



Features

- Connect up to 4 monitors - 2 local and 2 remote
- 3.5mm Stereo audio support and extension
- Extends a 1440 x 900 @ 60Hz signal up to 165 ft. (50 m) from the source
- Extends a 1024 x 768 @ 60Hz signal up to 500 ft. (150 m) from the source
- EDID copy feature ensures optimal display compatibility
- Built-in equalization control allows for adjustment of the video image
- All operating systems are supported
- Plug-and-play; no software or drivers are required
- HDCP compliant

Specifications

OVERVIEW	
UPC Code	037332182647
Product Type	Extender Kit
AC Adapter	Input: 100-240V, 50/60Hz, 0.5A; Output: 5V, 2A, 4.5 ft.
Technology	VGA/SVGA; Stereo Audio; Cat5/5e; Cat6
VIDEO	
Max Supported Video Resolution	1440x900 @ 60Hz

Highlights

- Extends a VGA + Stereo Audio signal up to 500 ft.
- Connect up to four VGA monitors: 2 Local and 2 Remote
- EDID copy feature ensures optimal display compatibility

System Requirements

- PC with VGA video output and 3.5mm Stereo output
- Monitors with VGA input; speakers with 3.5mm Stereo input

Package Includes

- Transmitter Unit
- Receiver Unit
- (2) External Power Supplies with NEMA 1-15P Plug (Input: 100-240V, 50/60Hz, 0.5A Output: 5V, 2A, 4.5 ft.)
- Screwdriver for equalization adjustment
- Owner's manual



Max 720P Range (ft)	165
Max 1280 x 720 (720p) Range (ft)	165
Transmitter Video Input	VGA
Transmitter - Number of Video Outputs	2
Transmitter - Local Display Output	VGA
Receiver/Transceiver Video Output	VGA
Receiver - Number of Video Outputs	2
Range Extension using other Tripp Lite product	1000ft @ 1024 x 768 (60Hz) 500ft @ 1920 x 1440 (60Hz)
Recommended Cabling	Solid Wire Cat6 Cables (Tripp Lite's N202-Series)
Other Tripp Lite product used to extend range	B132-110A
HDR Support	No
Maximum Signal Range (ft)	500
Maximum Signal Range (m)	152
Maximum Signal Range Details	500 ft @ 1024 x 768 (60Hz) 165 ft @ 1440 x 900 (60Hz)
AUDIO	
Audio Input	3.5mm
Audio Output	3.5mm
Audio Specification	Stereo Audio
POWER	
Power Source	Transmitter and Receiver (Included)
Power Source Type	AC Adapter
AC Plug Type	NEMA 1-15P
External Power Supply Input Specs (V / Hz / A)	100-240V / 50-60Hz / 0.5A
External Power Supply Output Specs (V / A)	5V/2A
External Power Supply Cord Length (ft.)	4.5
External Power Supply Cord Length (m.)	1.38
External Power Supply DC Barrel Connector Specs	OD: 5.5 x 2.1 x 7.5mm, Positive Pin, Negative Sleeve
External Power Supply Certifications	FCC; PSE; TUV; UL; cUL
Power Over Cable (PoC) Support	No
USER INTERFACE, ALERTS & CONTROLS	



LED Indicators	TX & RX: Red (Power); EDID (Orange); RJ45: Green (Connection), Orange (Data Transmission)
PHYSICAL	
Color	Black
Included Mounting Accessories	Wallmount
Number of Displays	4
Optional Mounting Accessory Notes	Can DIN Mount using Tripp Lite Bracket B110-DIN-01
Form Factor/Mounting Options	Box; Wall-mount
Receiver Unit Dimensions (hwd / in.)	4.53 x 1.06 x 2.46
Receiver Unit Weight (lbs.)	0.5
Shipping Dimensions (hwd / cm)	5.59 x 15.75 x 21.34
Shipping Dimensions (hwd / in.)	2.20 x 6.20 x 8.40
Shipping Weight (kg)	0.77
Shipping Weight (lbs.)	1.70
Transmitter Unit Dimensions (hwd / in.)	4.53 x 1.06 x 2.46
Transmitter Unit Weight (lbs.)	0.5
Unit Dimensions (hwd / cm)	Transmitter: 2.69 x 11.43 x 6.2 Receiver: 2.69 x 11.43 x 6.2
Unit Packaging Type	Box
Housing	Metal
ENVIRONMENTAL	
Operating Temperature Range	32 to 122 F (0 to 50 C)
Storage Temperature Range	-4 to 158 (-20 to 70 C)
Relative Humidity	10% to 90% RH, Non-Condensing
COMMUNICATIONS	
Max 1024 x 768 Range (ft)	500
Max 480P Range (ft)	500
Max 1440 x 900 Range (ft)	165
Max 480i Range (ft)	500
Max 640 x 480 Range (ft)	500
Max 800 x 600 Range (ft)	500
EDID Compatible	Yes
IR Remote Extension Support	No
RS-232 Serial Extension Support	No



USB Extension Support	No
CONNECTIONS	
Ports	2
Side A - Connector 1	(3) HD15 (FEMALE)
Side A - Connector 2	RJ45 (FEMALE)
Side A - Connector 3	3.5MM (FEMALE)
Side B - Connector 1	(2) HD15 (FEMALE)
Side B - Connector 2	RJ45 (FEMALE)
Side B - Connector 3	3.5MM (FEMALE)
FEATURES & SPECIFICATIONS	
Driver Required	No
Built-In Equalizer	Yes
STANDARDS & COMPLIANCE	
Certifications	Tested to FCC, RoHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[B130-202A](#)