

Multi-Device Charging Cart, 32 USB Ports, iPad and Android Tablets, Wall-Mount Option, White

MODEL NUMBER: **CSC32USBW**



Locking steel cart provides 2.4A USB charging, syncing, secure storage and cord management for up to 32 tablets and other devices. Recommended for education, office, commercial, retail, industrial and healthcare environments.

Features

Fast Charging

- 32 USB ports provide fastest charging supported by each device, up to 2.4A per port
- Recommended for iPad, Android, Surface and Kindle tablets
- Also charges mobile phones and other USB devices
- Fits tablets with cases (up to 16.5 x 10.5 x 1.5 in. with cord)
- 10-ft. (3.05 m) AC input cord with NEMA 5-15P plug reaches distant outlets

Convenient Syncing

- USB uplink port connects to host computer for wired syncing
- Supports wireless syncing and simultaneous syncing/charging (up to 1.5A per port during wired syncing)

Comprehensive Protection

- Sturdy steel construction and powder-coated finish promote long-term durability
- Doors lock with included keys to help prevent device theft, damage or tampering
- 3-point locking mechanism latches doors at top, middle and bottom
- Built-in hasp and user-supplied padlock can replace or supplement built-in lock
- Rear ports accommodate user-supplied bicycle cable or chain lock
- Flow-through ventilation helps prevent devices from overheating
- Protective shelves specially coated to avoid device scratches and scuffs

Highlights

- Fast 2.4A USB charging and syncing for 32 tablets
- Secures devices in locking, vented, wall-mountable steel cart
- Protective shelves with removable dividers and cord management
- Wide-grip handle and locking casters with non-marking wheels
- Ships ready for quick, easy installation

Package Includes

- CSC32USBW 32-Device USB Charging Station Cart, White
- Cart handle
- Input cord wrap
- Hex key
- Detachable 10-ft. (3.05 m) AC input cord
- Mounting hardware for handle and cord wrap
- (2) Keys
- Owner's manual



- Cord access ports with rubber grommets protect against abrasions
- Solid top work surface helps avoid accidental drips and spills that could damage devices

Clutter-Reducing Organization

- USB ports and charging cords store out of sight
- Shelves include charging cord access ports for each device
- Toolless trim panel permits quick access to cords

Convenient Mobility

- Large swivel casters with non-marking wheels improve ride over uneven surfaces
- Casters lock to help prevent unwanted movement at rest
- Reversible wide-grip handle assists cart control
- Reversible cord wrap keeps input cord out of the way when moving cart
- Compact cart fits in same space as typical utility cart

Flexible Configuration

- Ships ready for quick, easy installation—just attach handle and cord wrap
- Split front doors open 180 degrees for improved device and service access
- Rear-panel mounting slots support optional wall-mount installation
- Removable dividers accommodate thicker devices
- Firmware upgrade port for future updates

Specifications

OVERVIEW	
UPC Code	037332194695
Product Type	Multi-Device Charger
Charging Form Factor	Mobile Cart
Functions	Charge; Secure; Sync
Device Compatibility	Tablet; Phone
Device Slots	32
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Voltage Compatibility (VAC)	110; 120
Input Frequency	50 / 60 Hz (auto-select)
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	10



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Input Cord Length (m)	3.05
CHARGING	
Number of Charging Ports	32
Total Charging Amps	80A
Total Charging Watts	400
Charging Method	USB
Charging Port Type	USB A (FEMALE)
Charging Ports Details	Pass through
Charging Ports / Amps	(32) 2.4A
Overcharge Protection	Yes
Charging Amps per Port	2.4A
PHYSICAL	
Color	White
Antimicrobial Coating	No
Charging Station Form Factor	Mobile Cart
Material of Construction	Steel
Shipping Dimensions (hwd / cm)	101.50 x 59.99 x 85.50
Shipping Dimensions (hwd / in.)	39.96 x 23.62 x 33.66
Shipping Weight (kg)	70.50
Shipping Weight (lbs.)	155.43
Slot Dimensions - Bottom (hwd / in.)	10.5 x 1.5 x 15.4
Slot Dimensions - Bottom (hwd / mm)	267.3 x 38.2 x 390.5
Slot Dimensions - Top (hwd / in.)	10.5 x 1.5 x 15.4
Slot Dimensions - Top (hwd / mm)	267.3 x 38.2 x 390.5
Unit Dimensions (hwd / cm)	91.69 x 88.39 x 54.86 (with handle installed)
Unit Dimensions (hwd / in.)	36.1 x 34.8 x 21.6 (with handle installed)
Unit Weight (kg)	59.27
Unit Weight (lbs.)	130.67
Number of Shelves	2
ENVIRONMENTAL	
Power Consumption (Watts)	112
SPECIAL FEATURES	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Cord Management	Yes
EMI/RFI Line Noise Protection	Yes
Locking	Yes
Lock Type	Key
Built-In Circuit Breaker	Yes
Overcurrent Protection	Yes
Flow-Through Ventilation	Yes
UV Sterilization	No
STANDARDS & COMPLIANCE	
Certifications	Tested to EIA-310-E, FCC & IEC Class B, UL 60950 (Power Component)
Approvals	RoHS
NOM (Mexico)	Tested to NOM (Mexico)
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty
CATEGORY PAGE FILTERS (Y/N ONLY)	
External Receptacle	No

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[CSC32USBW](#)