

Full Motion Ceiling Mount for 23" to 42" TVs and Monitors.

MODEL NUMBER: DCTM



Highlights

- Fits most flat-panel displays from 23 to 42 in.
- One-touch adjustment for comfortable viewing
- 90° swivel and -20° tilt for wide range of motion
- Supports up to 66 lbs (30 kgs)

Package Includes

- DCTM
- Hardware packet
- Owner's Manual

Suspends a flat-panel television, monitor or other display from the ceiling, which saves valuable wall and floor space. Ideal for home theaters, classrooms, boardrooms, hotels, bars and restaurants.

Description

The DCTM Full Motion Ceiling Mount saves valuable wall and floor space by suspending your flat-panel television, monitor or other display from the ceiling. Ideal for home theaters, classrooms, boardrooms, hotels, bars and restaurants, it fits most flat-panel displays from 23 to 42 inches. The DCTM adjusts with one easy touch to customize your viewing at any time. A 90° swivel and -20° tilt capability minimizes glare and provides comfortable viewing from multiple angles. The durable all-metal pole extends from 24 to 34 inches and supports up to 66 lbs (30 kgs). The scratch-resistant powder-coated finish tolerates frequent handling and blends with any décor. Installation hardware is included. Conforms to VESA-compliant displays with any of the following mounting hole patterns: 75 x 75 mm, 75 x 100 mm, 75 x 200 mm, 100 x 75 mm, 100 x 100 mm, 100 x 200 mm, 200 x 75mm, 200 x 100 mm and 200 x 200 mm.

Features

Save Valuable Wall and Floor Space Suspends flat-panel TV, monitor or other display from ceiling Fits most flat-panel devices from 23 to 42 in. Installation hardware included Ideal for home theaters, classrooms, boardrooms, hotels, bars and restaurants

Convenient One-Touch Adjustment 90° swivel and -20° tilt capability provides comfortable viewing from multiple angles

Durable Metal Construction Supports up to 66 lbs (30 kgs) Pole extends from 24 to 34 in. Scratch-resistant powder-coated finish blends with any décor

VESA Compliance Supports the following VESA mounting hole patterns: 75 x 75 mm, 75 x 100 mm, 75 x 200 mm, 100 x 75 mm, 100 x 100 mm, 100 x 200 mm, 200 x 75mm, 200 x 100 mm and 200 x 200 mm

Specifications

OVERVIEW	
UPC Code	037332223456
Device Compatibility	Monitor/HDTV



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

PHYSICAL	
Color	Black
VESA Pattern (mm)	100x100; 100x200; 100x75; 200x100; 200x200; 200x75; 75x100; 75x200; 75x75
Degrees of Motion	-20 Tilt; 90 Swivel
Material of Construction	Steel
Maximum Screen Size (cm)	106.68
Maximum Screen Size (in.)	42
Maximum Weight Capacity (kg)	30
Maximum Weight Capacity (lbs.)	66
Min/Max Arm Extension (in.)	24 - 34
Minimum Screen Size (in.)	23
Minimum Screen Size (cm)	58.42
Motion	Full
Mounting Location	Ceiling
Number of Displays	1
Shipping Dimensions (hwd / cm)	53.59 x 24.89 x 51.05
Shipping Dimensions (hwd / in.)	21.10 x 9.80 x 20.10
Shipping Weight (kg)	2.40
Shipping Weight (lbs.)	5.30
Unit Dimensions (hwd / cm)	13.72 x 16 x 96.52
Unit Dimensions (hwd / in.)	5.4 x 6.3 x 38
Unit Weight (kg)	2.22
Unit Weight (lbs.)	4.9
FEATURES & SPECIFICATIONS	
Tools Necessary	Yes
SPECIAL FEATURES	
Cord Management	No
Security Lock	No
STANDARDS & COMPLIANCE	
Approvals	RoHS3, REACH and CE
WARRANTY	
Product Warranty Period (Worldwide)	5-year limited warranty



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:
<https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[DCTM](#)