

Full-Motion Universal Tablet Desk Clamp for 7 in. to 10 in. Tablets

MODEL NUMBER: DDR0710SC



Highlights

- Clamps to most flat surfaces up to 1.6 in. thick
- Fits most tablets ranging from 7 to 10 in.
- Attaches above or below your workspace's surface
- Rotates 360° in portrait and landscape orientations
- Supports up to 2.2 lbs (1 kg)

Package Includes

- DDR0710SC Full-Motion Universal Tablet Desk Clamp
- Installation instructions

Mount your tablet above or below the surface of your desk, table or workstation to free up valuable space. Customize the tablet's angle and height for comfortable viewing.

Description

The DDR0710SC Full-Motion Universal Tablet Desk Clamp attaches to your desk, table or workstation, allowing you to mount your tablet above or below it and free up valuable workspace. Upside-down mounting to a cabinet or workstation lets you read recipes or instructions at eye level. Clamps firmly to most flat surfaces up to 1.6 inches thick. Flexible arm lets you adjust your tablet's angle and height to fit your environment and comfort level. Fits tablets ranging from 7 to 10 inches. Rotates 360°, so you can view your tablet in portrait and landscape orientations. Easy installation in seconds with no tools necessary. Supports tablets up to 2.2 lbs (1 kg).

Features

Attaches to Most Desks, Tables and Workstations

- Clamps securely to most flat surfaces up to 1.6 in. thick
- Fits most tablets from 7 to 10 in.
- Mounts above or below your workspace's surface
- Upside-down mounting lets you read recipes or instructions at eye level
- Flexible arm lets you adjust height and angle for comfortable viewing
- Full 360° rotation in both portrait and landscape orientations

Installs in Seconds

- No tools necessary
- Supports up to 2.2 lbs (1 kg)

Specifications



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

OVERVIEW	
UPC Code	037332190543
Device Compatibility	Tablet
PHYSICAL	
Color	Black
Degrees of Motion	-180/+180 Tilt; 360 Swivel; 360 Rotate
Material of Construction	Metal, Plastic
Maximum Screen Size (cm)	25.4
Maximum Screen Size (in.)	10
Maximum Weight Capacity (kg)	1
Maximum Weight Capacity (lbs.)	2.2
Minimum Screen Size (in.)	7
Minimum Screen Size (cm)	17.78
Motion	Full
Mounting Location	Desk Clamp
Shipping Dimensions (hwd / cm)	8.00 x 20.98 x 29.01
Shipping Dimensions (hwd / in.)	3.15 x 8.26 x 11.42
Shipping Weight (kg)	0.78
Shipping Weight (lbs.)	1.72
Unit Dimensions (hwd / cm)	18.21 x 24.42 x 6.99
Unit Dimensions (hwd / in.)	7.17 x 9.61 x 2.75
Unit Weight (kg)	0.58
Unit Weight (lbs.)	1.28
FEATURES & SPECIFICATIONS	
Tools Necessary	No
SPECIAL FEATURES	
Cord Management	No
STANDARDS & COMPLIANCE	
Approvals	RoHS3, REACH
WARRANTY	
Product Warranty Period (Worldwide)	5-year limited warranty



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:
<https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[DDR0710SC](#)