

Single Monitor Mount Stand for 10" to 32" Flat-Screen Displays

MODEL NUMBER: DDR1032SE



Mounts your monitor on a base to free up valuable space on your desk, table or workstation. Ideal for home or office use.

Description

The VESA-compliant DDR1032SE Single Monitor Mount Stand mounts your monitor on a sturdy base, allowing you to free up valuable workspace on your desk, table or workstation. Ideal for home and office, the DDR1032SE fits most flat-panel displays from 10 to 32 inches.

Position your monitor with one-touch ease to optimize viewing angle and height to fit your environment and comfort level. A 180° swivel and -15° to +15° tilt capability minimizes glare and provides comfortable viewing from multiple angles. A 360° rotation lets you view your monitor in portrait or landscape orientation.

Mount supports up to 36 lbs (16.3 kgs). The durable all-metal frame with scratch-resistant powder-coated finish tolerates frequent handling and blends with any décor. Mounting hardware is included. Conforms to VESA-compliant displays with any of the following mounting hole patterns: 75 x 75 mm, 75 x 100 mm, 100 x 75 mm, and 100 x 100 mm.

Features

Mounts Your Monitor on a Base Frees up valuable workspace on your desk, table or workstation Fits most flat-panel displays from 10 to 32 in. Mount adjusts independently for viewing angle and height Ideal for home and office use

Convenient One-Touch Adjustment 180° swivel and -15° to +15° tilt capability provides comfortable viewing Full 360° rotation for viewing in portrait or landscape orientation

Durable Metal Construction Mount supports up to 36 lbs (16.3 kgs) Scratch-resistant powder-coated finish blends with any décor Mounting hardware included

VESA Compliance Supports the following VESA mounting hole patterns: 75 x 75 mm, 75 x 100 mm, 100 x 75 mm, and 100 x 100 mm

Highlights

- Fits most flat-panel displays from 10 to 32 in.
- One-touch adjustment for comfortable viewing
- 180° swivel and -15° to +15° tilt for wide range of motion
- Supports up to 36 lbs (16.3 kgs)

Package Includes

- Pole
- Base
- Mounting assembly
- Top cap
- (4) M6 screws
- (4) M4 screws
- (4) M6 lock washers
- (4) Washers
- (4) Spacers
- (2) Hex keys
- Owner's manual

Specifications

OVERVIEW	
UPC Code	037332181763
Device Compatibility	Monitor/HDTV



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

PHYSICAL	
Color	Black
VESA Pattern (mm)	100x100; 100x75; 75x100; 75x75
Degrees of Motion	-15/+15 Tilt; 180 Swivel; 360 Rotate
Material of Construction	Steel
Maximum Screen Size (cm)	81.28
Maximum Screen Size (in.)	32
Maximum Weight Capacity (kg)	16
Maximum Weight Capacity (lbs.)	36
Minimum Screen Size (in.)	10
Minimum Screen Size (cm)	25.4
Motion	Full
Mounting Location	Desktop
Number of Displays	1
Shipping Dimensions (hwd / cm)	16.76 x 29.46 x 46.74
Shipping Dimensions (hwd / in.)	6.60 x 11.60 x 18.40
Shipping Weight (kg)	4.22
Shipping Weight (lbs.)	9.30
Unit Dimensions (hwd / cm)	39.88 x 25.91 x 37.8
Unit Dimensions (hwd / in.)	15.7 x 10.2 x 14.9
Unit Weight (kg)	2.49
Unit Weight (lbs.)	5.50
FEATURES & SPECIFICATIONS	
Tools Necessary	Yes
SPECIAL FEATURES	
Cord Management	No
Security Lock	No
WARRANTY	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

<https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[DDR1032SE](#)