

Easy Pull Long-Run Display Cable - Type-A Analog PVC Trunk Cable, 100 ft. (30.5 m)

MODEL NUMBER: **EZA-100**



Description

Tripp Lite's EZA-100 100-ft. (30.5 m) Easy Pull VGA Trunk cable makes pulling video cable through conduit or confined areas a breeze. Threaded ends feature screw on pull-caps, which can be attached to fish tape. Choose from a variety of connector choices that easily screw on to the threaded ends of the trunk cable. Trunk cables are available in 35-ft. (10.67 m), 50-ft. (15.24 m), and 100-ft. (30.5 m) lengths, PVC and plenum rated. Cable ends are colored-coded green to denote VGA applications (Digital trunk cables are Yellow). Cable features triple-shielded construction with 75 ohm coax conductors for RGBHV signals supporting resolutions up to 1600 x 1200. Trunk also carries Audio signals when used with Easy Pull end kits that feature Audio connections.

Features

- Eliminates the need to field terminate VGA connectors
- Detachable, screw-on connectors
- Allows cable to be run according to code - inside conduit, drop ceilings, etc.
- At a diameter of 7/8 in., it makes pulling long cables fast and easy
- Protects entire cable from strain, dirt, debris and damage
- Choose from a variety of connector combinations for the perfect fit
- Available in 35-ft. (10.67 m), 50-ft. (15.24 m), and 100-ft. (30.5 m) lengths, both PVC and plenum rated
- Supports Video and Audio pass through depending on end kit used

Specifications

OVERVIEW	
UPC Code	037332141880

Highlights

- Versatile trunk cable allows for a variety of connection options
- At a diameter of 7/8 in., it easily pulls through conduit or confined spaces using the included end cap with integrated pull tab
- High quality RGB style VGA cable supports resolutions up to 1600 x 1200, as well as Audio pass through

Package Includes

- Easy Pull Type-A VGA Analog PVC Trunk Cable, 100-ft. (30.5 m)



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Technology	VGA/SVGA
PHYSICAL	
Color	Black; Green
Cable Length (ft.)	100
Cable Length (m)	30.5
Shipping Dimensions (hwd / cm)	5.08 x 24.13 x 25.40
Shipping Dimensions (hwd / in.)	2.00 x 9.50 x 10.00
Shipping Weight (kg)	1.77
Shipping Weight (lbs.)	3.90
CONNECTIONS	
Side A - Connector 1	DIN 14 PIN (FEMALE)
Side B - Connector 1	DIN 14 PIN (FEMALE)
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[EZA-100](#)