



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

FireWire 800 IEEE 1394b Hi-speed Cable (9pin/9pin M/M) 6 ft. (1.83 m)

MODEL NUMBER: **F015-006**



Highlights

- Twice the Speed of Original FireWire - Data Transfers to 800Mbps
- Meets FireWire 800 and 1394b Specifications
- Backward compatible to Original FireWire components

Package Includes

- 6-ft. (1.83 m) IEEE-1394b FireWire 800 Gold Hi-Speed 9pin/9pin Cable

Features

- Data transfer rates to 800Mbps
- Hot Pluggable - supports Plug-n-Play operation
- Premium triple-shielded cable with molded, Gold connectors
- Backward compatible with original FireWire systems and devices
- Compatible with PC, Mac, SUN, and other IEEE-1394b equipped systems

Specifications

OVERVIEW	
UPC Code	037332124623
Technology	FireWire
PHYSICAL	
Color	Black
Cable Length (ft.)	6
Cable Length (m)	1.8
Shipping Dimensions (hwd / cm)	21.59 x 17.53 x 1.27
Shipping Dimensions (hwd / in.)	8.50 x 6.90 x 0.50
Shipping Weight (kg)	0.08
Shipping Weight (lbs.)	0.17



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

CONNECTIONS	
Side A - Connector 1	9 PIN (MALE)
Side B - Connector 1	9 PIN (MALE)
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[F015-006](#)