

Internet Office 120V 900VA 480W Standby UPS, Ultra-Compact Desktop, USB

MODEL NUMBER: **INTERNET900U**



Description

Tripp Lite's INTERNET900U standby UPS offers complete protection for PCs, workstations and other sensitive electronics in an attractive, ultra-compact, mountable housing. Prevents data loss and system downtime by providing battery-supported AC output during brownouts and blackouts. 12 widely spaced output receptacles accommodate large transformer plugs without blocking outlets. 6 outlets provide full battery support and surge suppression for computers, monitors and other vital system components. 6 additional surge suppression-only outlets are ideal for printers and other accessories not requiring battery support. Single-line telephone suppression jacks protect directly connected modems, fax machines, cordless phones or other peripherals sharing a standard dialup or DSL phone line connection. USB communications with PowerAlert monitoring software and cabling enables a safe, unattended system shutdown. HID-compliant USB also enables integration with built-in power management and auto shutdown features of Windows and Mac OS X. Audible alarm and front panel LEDs offer status information regarding line and battery power operation. 900VA/480W power handling ability supports entry-level PCs for up to 45 min. during power failures. \$100,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only).

Features

- INTERNET900U standby UPS offers complete protection from blackouts, brownouts and surges on AC and tel/DSL dataline connections
- 12 widely spaced outlets accommodate large transformer plugs without blocking outlets
- 6 battery-supported outlets protect computers and vital system peripherals. 6 surge suppression-only outlets protect system accessories that do not require battery support
- Provides battery-derived AC output during blackouts and brownouts
- 900VA/480W power handling ability supports a variety of PCs, workstations and other sensitive

Highlights

- 900VA ultra-compact 120V standby UPS
- Maintains AC output during power failures
- 6 UPS battery supported outlets, 6 surge-only outlets
- USB, TEL/DSL protection, Wall mountable, 99% efficient
- NEMA 5-15P input plug and 12 NEMA 5-15R outlets
- This product is ENERGY STAR qualified for its ability to save customers money while helping to protect the environment

Package Includes

- INTERNET900U UPS system
- USB cable
- Instruction manual



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

electronics

- Supports entry-level PC systems up to 45 min. during blackouts
- Single-line tel/DSL surge suppression protects directly connected modems, fax machines or cordless phones sharing a single phone line connection
- USB port enables data-saving unattended shutdown when used with Tripp Lite's PowerAlert software, available via FREE download from www.tripplite.com/poweralert
- HID-compliant USB also enables integration with built-in power management and auto shutdown features of Windows and Mac OS X
- Supports Tripp Lite's Watchdog system service to restore operation to locked equipment through soft reboot of application/OS or hard power off/on reboot of connected equipment; ideal for unattended kiosk applications
- Space-saving ultra-compact housing
- Keyhole mounting flanges enable secure wallmount installation
- Optional [PDUB15](#) bypass PDU enables hot-swappable UPS replacement with no disruption to connected equipment
- \$100,000 [Ultimate Lifetime Insurance](#) protects connected equipment from surge damage (U.S., Canada, and Puerto Rico only)

Specifications

OUTPUT	
Output Volt Amp Capacity (VA)	900
Output Watt Capacity (Watts)	480
Nominal Output Voltage(s) Supported	110V; 115V; 120V
Nominal Voltage Details	115v nominal output in battery mode
Frequency Compatibility	60 Hz
Output Voltage Regulation (Battery Mode)	+/- 5%
Output Receptacles	(12) 5-15R
UPS Output Receptacles (Surge Suppression Only)	6 UPS outlets, 6 surge-only outlets
Hot-Swap PDU options	PDUB15 (2U / 8 5-15R outlets)
Output AC Waveform (AC Mode)	Sine wave
Output AC Waveform (Battery Mode)	PWM sine wave
INPUT	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Rated input current (Maximum Load)	10A
Nominal Input Voltage(s) Supported	120V AC
UPS Input Connection Type	5-15P; Right-Angled
Input Circuit Breakers	10A
UPS Input Cord Length (ft.)	6
UPS Input Cord Length (m)	1.8
Recommended Electrical Service	15A 120V
Input Phase	Single-Phase
BATTERY	
Half Load Runtime (min.)	8.2 min. (240w)
DC System Voltage (VDC)	12
Expandable Runtime	No
USER INTERFACE, ALERTS & CONTROLS	
Switches	Combination switch controls on/off power status and self-test operation
Audible Alarm	Audible alarm indicates power-failure and overload status
LED Indicators	2 LEDs indicate power status and overload/check battery status
SURGE / NOISE SUPPRESSION	
UPS AC Suppression Joule Rating	420
UPS AC Suppression Response Time	Instantaneous
UPS Dataline Suppression	1 line TEL/DSL (1 in / 1 out)
EMI / RFI AC Noise Suppression	Yes
PHYSICAL	
Included Mounting Accessory Description	Wallmount installation supported using keyhole mounting tabs
Installation Form Factors Supported with Included Accessories	Tower; Ultra-compact desktop
Primary Form Factor	Desktop
UPS Power Module Dimensions (hwd, in.)	3.1 x 12.2 x 6.9
UPS Power Module Dimensions (hwd, cm)	7.87 x 30.99 x 17.53
UPS Power Module Weight (lbs.)	8.7
UPS Power Module Weight (kg)	3.95



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

UPS Shipping Dimensions (hwd / in.)	4.6 x 15 x 9.8
UPS Shipping Dimensions (hwd / cm)	11.68 x 38.10 x 24.89
Shipping Weight (lbs.)	9.6
Shipping Weight (kg)	4.4
UPS Housing Material	ABS
Primary UPS Height (mm)	79
Primary UPS Width (mm)	310
Primary UPS Depth (mm)	175
Shipping Height (mm)	117
Shipping Width (mm)	381
Shipping Depth (mm)	249
ENVIRONMENTAL	
Operating Temperature Range	+32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius.
Storage Temperature Range	+5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius.
Relative Humidity	0 to 95%, non-condensing
AC Mode BTU / Hr. (Full Load)	14
Battery Mode BTU / Hr. (Full Load)	336
AC Mode Efficiency Rating (100% Load)	99%
COMMUNICATIONS	
Communications Interface	USB (HID enabled)
PowerAlert Software	For local monitoring via the UPS's built-in USB port, download PowerAlert Local software at http://www.tripplite.com/poweralert
Communications Cable	RJ to USB interface cable included
WatchDog Compatibility	Supports Watchdog application, OS and hard-reboot restart options for remote applications
Network UPS Tools Compatibility	NUT compatible. See the full list of Tripp Lite NUT compatible UPS systems at http://www.networkupstools.org/stable-hcl.html?manufacturer=Tripp Lite
LINE / BATTERY TRANSFER	
Transfer Time	2-4 milliseconds
Low Voltage Transfer to Battery Power (Setpoint)	99
High Voltage Transfer to Battery Power (Setpoint)	139



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

SPECIAL FEATURES	
Cold Start (Startup in Battery Mode During a Power Failure)	Cold-start operation supported
Green Energy-Saving Features	Greater than 95% efficiency - GREEN UPS
CERTIFICATIONS	
UPS Certifications	Tested to UL1778 (USA); Tested to CSA (Canada); Tested to NOM (Mexico); Meets FCC Part 15 Category B (EMI); ENERGY STAR Qualified
WARRANTY	
Product Warranty Period (U.S. & Canada)	3-year limited warranty
Product Warranty Period (Latin America)	3-year limited warranty
Product Warranty Period (International)	2-year limited warranty
Product Warranty Period (Mexico)	3-year limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$100,000 <u>Ultimate Lifetime Insurance</u>

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[INTERNET900U](#)