



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

NOTE: if you need to connect a Cisco device to a newer laptop that doesn't have an RJ45 network port, we recommend Tripp Lite's U209-006-RJ45-X USB to RJ45 Cisco Serial Rollover Cable.

## Cisco Console Rollover Cable (RJ45 M/M), 6 ft. (1.83 m)

MODEL NUMBER: **N205-006-BL-FCR**



Connects your computer or laptop to a Cisco router, server, switch or other Cisco networking equipment.

### Features

#### Connects Your Computer or Laptop to a Cisco Networking Device

- Direct replacement for lost or damaged Cisco rollover cable
- Ideal for routers, servers, switches and other Cisco networking equipment
- Male RJ45 connectors
- 32 AWG copper wire
- Rugged PVC jacket

## Specifications

OVERVIEW	
UPC Code	037332194183
Technology	Cat6
PHYSICAL	
Color	Blue
Cable Shielding	UTP
Cable Jacket Material	PVC
Number of Conductors	4 Pair

### Highlights

- Direct replacement for existing Cisco rollover cable
- Works with new and old Cisco equipment
- 32 AWG copper wire
- Rugged PVC jacket
- Male RJ45 connectors

### System Requirements

- Computer or laptop with RJ45 port
- Cisco networking hardware with RJ45 console port

### Package Includes

- N205-006-BL-FCR Cisco Console Rollover Cable (RJ45 M/M), 6 ft.



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Conductor Material	Stranded Copper
Conductor Gauge	32 AWG
Cable Length (ft.)	6
Cable Length (m)	1.8
Cable Length (in.)	72
Cable Length (cm)	182.9
Shipping Dimensions (hwd / cm)	17.78 x 22.86 x 1.27
Shipping Dimensions (hwd / in.)	7.00 x 9.00 x 0.50
Shipping Weight (kg)	0.06
Shipping Weight (lbs.)	0.14
<b>COMMUNICATIONS</b>	
Bandwidth per TIA Standard	250 MHz
Maximum Bandwidth as Tested	N/A
Maximum Data Rate	1Gbps
<b>CONNECTIONS</b>	
Side A - Connector 1	RJ45 (MALE)
Side A - Connector 2	RJ45 (MALE)
Side B - Connector 1	RJ45 (MALE)
Connector Type	Molded; Rollover
<b>SPECIAL FEATURES</b>	
IP68 Rated	No
Snagless Connector	No
Antibacterial	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Certifications	RoHS
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[N205-006-BL-FCR](#)