



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

NOTE: if you need to connect a Cisco device to a newer laptop that doesn't have an RJ45 network port, we recommend Tripp Lite's U209-006-RJ45-X USB to RJ45 Cisco Serial Rollover Cable.

Cisco Console Rollover Cable (RJ45 M/M), 10 ft. (3.05 m)

MODEL NUMBER: **N205-010-BL-FCR**



Connects your computer or laptop to a Cisco router, server, switch or other Cisco networking equipment.

Description

The N205-010-BL-FCR Cisco Console Rollover Cable is a direct replacement for a lost or damaged Cisco rollover cable. This 10-ft. (3.05 m) blue cable connects your desktop computer or laptop to the console port of a new or older Cisco device, including routers, servers, switches and other Cisco networking equipment. Male RJ45 connectors, 32 AWG copper construction and a rugged PVC jacket ensure excellent connectivity and a long life.

Features

Connects Your Computer or Laptop to a Cisco Networking Device

- Direct replacement for lost or damaged Cisco rollover cable
- Ideal for routers, servers, switches and other Cisco networking equipment
- Male RJ45 connectors
- 32 AWG copper wire
- Rugged PVC jacket

Specifications

OVERVIEW	
UPC Code	037332194190
Technology	Cat6

Highlights

- Direct replacement for existing Cisco rollover cable
- Works with new and older Cisco equipment
- 32 AWG copper wire
- Rugged PVC jacket
- Male RJ45 connectors

System Requirements

- Computer or laptop with RJ45 port
- Cisco networking hardware with RJ45 console port

Package Includes

- N205-010-BL-FCR Cisco Console Rollover Cable (RJ45 M/M), 10-ft. (3.05 m)



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

PHYSICAL	
Color	Blue
Cable Shielding	UTP
Cable Jacket Material	PVC
Number of Conductors	4 Pair
Conductor Material	Stranded Copper
Conductor Gauge	32 AWG
Cable Length (ft.)	10
Cable Length (m)	3
Cable Length (in.)	120
Cable Length (cm)	304.8
Shipping Dimensions (hwd / cm)	17.78 x 22.86 x 1.27
Shipping Dimensions (hwd / in.)	7.00 x 9.00 x 0.50
Shipping Weight (kg)	0.05
Shipping Weight (lbs.)	0.10
COMMUNICATIONS	
Bandwidth per TIA Standard	250 MHz
Maximum Bandwidth as Tested	N/A
Maximum Data Rate	1Gbps
CONNECTIONS	
Side A - Connector 1	RJ45 (MALE)
Side A - Connector 2	RJ45 (MALE)
Side B - Connector 1	RJ45 (MALE)
Connector Type	Molded; Rollover
SPECIAL FEATURES	
IP68 Rated	No
Snagless Connector	No
Antibacterial	No
STANDARDS & COMPLIANCE	
Certifications	RoHS
WARRANTY	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Product Warranty Period (Worldwide)	Lifetime limited warranty
--	---------------------------

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:
<https://www.tripplite.com/products/product-certification-agencies>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[N205-010-BL-FCR](#)